

NOTES

MATERIAL

1.HOUSING MATERIAL: GLASS FILLED POLYESTER UL94V-0.

2.CONTACT MATERIAL: PHOSPHOR BRONZE $\phi 0.46\text{mm}$.

3.PLATING: GOLD FLASH PLATING OVER NICKEL.

4.SHIELD: BRASS T0.20mm 40u" NICKEL PLATED.

ELECTRICAL

1.VOLTAGE RATING: 125 VAC RMS.

2.CURRENT RATING: 1.5 AMP.

3.CONTACT RESISTANCE: 40 MILLIOHMS MAX.

4.INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC .

5.DIELECTRIC DIELECTRIC

RESISTANCE: 500V DC RMS 50Hz. 1MIN.

MECHANICAL




1.DURRABILITY: 750 CYCLES MIN.

2.MATING/UNMATING FORCE: 2.24 KG.F MAX.



ENVIRONMENTAL:

1.STORAGE: $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.2.OPERATION: $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.

焊脚尺寸以顺畅过孔规为准



8	—
7	—
6	RX—
5	—
4	—
3	RX+
2	TX—
1	TX+
PIN	说明

PCBLAYOUT
TOL:±0.05

DIMENSION IN mm		厦门市辛译精密电子有限公司					
TOLERANCE UNLESS OTHERWISE SPECIFIED		Xiamen XinYi Xyconn Electronics Co.,Ltd					
.X±0.35	X.*±3	APR.	Alex	TITLE: RJ45 56B雙芯線 帶加強結構 DIP			
.XX±0.25	.X*±2	CHK.	Jack	DWG NO. XY-RJ45R0-8PC-202			
.XXX±0.15	.XX*±1*			PROJ. 		CUSTOMER DRAWING	
		DRA.	Can	SIZE A4	SCALE 1:1	SHEET 1/1	REV. A