





REV.	Q'TY	ECN. NO.	APR.	DATE



SPECIFICATIONS
 Current Rating: 3Amps
 Insulation Resistance: 1000MΩ Min
 Contact Resistance: 20mΩ Max
 Withstanding Voltage: AC 1000V
 Operation Temperature: -40°to+105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester(UL 94V-0)
 Contact Plating: Gold Flash
 Max.Processing Temp: 240°C for30-60seconds
 (260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
PM2.54-2-1P-W	2*1	0.00	2.54
PM2.54-2-2P-W	2*2	2.54	5.08
PM2.54-2-3P-W	2*3	5.08	7.62
PM2.54-2-4P-W	2*4	7.62	10.16
PM2.54-2-5P-W	2*5	10.16	12.70
PM2.54-2-6P-W	2*6	12.70	15.24
PM2.54-2-7P-W	2*7	15.24	17.78
PM2.54-2-8P-W	2*8	17.78	20.32
PM2.54-2-9P-W	2*9	20.32	22.86
.....
PM2.54-2-40P-W	2*40	(PIN-1)X2.54	(PIN)X2.54



RECOMMEND P.C.B LAYOUT
 PCB TOLERANCE:±0.05 (TOP VIEW)

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd		
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 2.54FH H8.5 2xnPin 90# Y# PC3.2 PB12.7 6T
.X±0.3	X.*± 5°	CHK.	Jack	DWG NO. PM2.54-2-NP-W
.XX±0.2	.X*± 1	DRA.	Can	PROJ. CUSTOMER DRAWING
.XXX±0.1	.XX*± 0.5	SIZE	A4	SCALE 1:1 SHEET 1/1 REV. A