




## 技术指标:

1. 塑件表面应光洁, 无毛边, 无明显收缩、缺陷、裂纹等现象。
2. 温度范围:  $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC/DC(=等效)。
4. 接触电阻: 50m $\Omega$ 。
5. 绝缘电阻:  $\geq 500\text{M}\Omega$ 。
6. 耐电压: 150V AC/Minute



| P/N                   | PIN   | DIM A | DIM B | DIM C | DIM D |
|-----------------------|-------|-------|-------|-------|-------|
| FPC13-YSZ0.5-5ABRH52  | 5     | 6.70  | 2.00  | 4.00  | 4.45  |
| FPC13-YSZ0.5-6ABRH52  | 6     | 7.20  | 2.50  | 4.50  | 4.95  |
| FPC13-YSZ0.5-7ABRH52  | 7     | 7.70  | 3.00  | 5.00  | 5.45  |
| FPC13-YSZ0.5-8ABRH52  | 8     | 8.20  | 3.50  | 5.50  | 5.95  |
| FPC13-YSZ0.5-9ABRH52  | 9     | 8.70  | 4.00  | 6.00  | 6.45  |
| FPC13-YSZ0.5-10ABRH52 | 10    | 9.20  | 4.50  | 6.50  | 6.95  |
| FPC13-YSZ0.5-11ABRH52 | 11    | 9.70  | 5.00  | 7.00  | 7.45  |
| FPC13-YSZ0.5-12ABRH52 | 12    | 10.20 | 5.50  | 7.50  | 7.95  |
| FPC13-YSZ0.5-13ABRH52 | 13    | 10.70 | 6.00  | 8.00  | 8.45  |
| FPC13-YSZ0.5-14ABRH52 | 14    | 11.20 | 6.50  | 8.50  | 8.95  |
| FPC13-YSZ0.5-15ABRH52 | 15    | 11.70 | 7.00  | 9.00  | 9.45  |
| FPC13-YSZ0.5-16ABRH52 | 16    | 12.20 | 7.50  | 9.50  | 9.95  |
| .....                 | ..... | ..... | ..... | ..... | ..... |
| FPC13-YSZ0.5-66ABRH52 | 66    | 37.20 | 32.50 | 34.50 | 34.95 |
| FPC13-YSZ0.5-67ABRH52 | 67    | 37.70 | 33.00 | 35.00 | 35.45 |
| FPC13-YSZ0.5-68ABRH52 | 68    | 38.20 | 33.50 | 35.50 | 35.95 |
| FPC13-YSZ0.5-69ABRH52 | 69    | 38.70 | 34.00 | 36.00 | 36.45 |
| FPC13-YSZ0.5-70ABRH52 | 70    | 39.20 | 34.50 | 36.50 | 36.95 |

| 序号 | 品名                   | 材质            |
|----|----------------------|---------------|
| 1  | 0.5 Pitch 连接器(H=5.2) | LCP UL94V-0 纯 |
| 2  | 0.5 Pitch 连接器(H=5.2) | LCP UL94V-0 纯 |
| 3  | 0.5 Pitch 连接器(H=5.2) | 铜合金/表面镀金      |
| 4  | 0.5 Pitch 连接器(H=5.2) | 铜合金/表面镀金      |

| DIMENSION IN mm                      |           | 厦门市辛译精密电子有限公司<br>Xiamen XinYi Xyeconn Electronics Co.,Ltd |                                                                                             |           |                  |        |  |  |
|--------------------------------------|-----------|-----------------------------------------------------------|---------------------------------------------------------------------------------------------|-----------|------------------|--------|--|--|
| TOLERANCE UNLESS OTHERWISE SPECIFIED |           |                                                           |                                                                                             |           |                  |        |  |  |
| .X±0.5                               | X.*± 0.05 | APR.<br>Alex                                              | TITLE: 0.5 Pitch 连接器(H=5.2)                                                                 |           |                  |        |  |  |
| .XX±0.2                              | .X*± 1    | CHK.<br>Jack                                              | DWG NO. FPC13-YSZ0.5-NABRH52                                                                |           |                  |        |  |  |
| .XXX±0.1                             | .XX*±     | DRA.<br>Can                                               | PROJ.  |           | CUSTOMER DRAWING |        |  |  |
|                                      |           |                                                           | SIZE A4                                                                                     | SCALE 1:1 | SHEET 1/1        | REV. A |  |  |