




1. 额定负载: DC50V 0.3A
2. 接触电阻: 100毫欧以下
3. 绝缘电阻: 100兆欧以上
4. 耐压: AC 500V
5. 力度: 250⁺100gf
6. 寿命: 10000次
7. 回流焊温度: 255 ° ± 5 °
8. 手焊: 350⁺10度

L2-6

8					TOLXPANCE						
7					UNLESS SPECIFEN						
6					WITHIN 1.5mm: ±0.1mm	A	20190717	初版			
5	CONTACT	PBS STRIP	1	AG PLATEN	OVER 1.5mm:±0.2mm	ISSUE	DATE	DESCRIPTIONS OF REVISION		APPD.	
4	TERMINAL	BRASS STRIP	4	AG PLATEN OVER Ni PLATEN	MODEL: HX SK12D07VG2-T			UNIT:mm	DRWG NO:		
3	BASB	PHENOLIC RESIN	1	NATURAL							
2	KNOB	POM	1	BLACK	 韩下® 深圳市韩下电子有限公司			SCALE:3:1	DWN.	黄彬	2020.8.25
1	FRAME	STEEL STRIP	1	Ni PLATEN					CHK"D	张伟	2020.8.25
NO.	PARTS	MATERLALS	Q"TY	FINISH							