





2P



3P



4P



5P-15P

技术指标:

- 1.温度范围Temperatuer Range:-25°C~105°C.
- 2.额定电压Voltage Rating:125V AC,DC.
- 3.耐电压Dielectric Strength:500V AC/minute.
- 4.接触电阻Contact Resistance:≤20mΩ
- 5.绝缘电阻Insulation esistance:≥1000MΩ.
- 6.额定电流Current Rating: 3A AC,DC(AWG22#).
- 7.适用线径Applicable wire insulation:AWG22#-26#

1	MX2.0 B型WTB无锁公头胶壳	PBT/白色
序号	名称	材质

P/N	PIN	DIM A	DIM B	DIM C
BX-MX2.0-2PJK-W	2	2.00	4.70	8.00
BX-MX2.0-3PJK-W	3	4.00	6.70	8.10
BX-MX2.0-4PJK-W	4	6.00	8.70	10.00
BX-MX2.0-5PJK-W	5	8.00	10.70	12.00
BX-MX2.0-6PJK-W	6	10.00	12.70	14.00
BX-MX2.0-7PJK-W	7	12.00	14.70	16.00
BX-MX2.0-8PJK-W	8	14.00	16.70	18.00
BX-MX2.0-9PJK-W	9	16.00	18.70	20.00
BX-MX2.0-10PJK-W	10	18.00	20.70	22.00
BX-MX2.0-11PJK-W	11	20.00	22.70	24.00
BX-MX2.0-12PJK-W	12	22.00	24.70	26.00
BX-MX2.0-13PJK-W	13	24.00	26.70	28.00
BX-MX2.0-14PJK-W	14	26.00	28.70	30.00
BX-MX2.0-15PJK-W	15	28.00	30.70	32.00

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-MX2.0-NPJK-W		版本 REV.	A
			X.±0.50	±1°	审核 CHECK	EVA			品名 TITLE	MX2.0 B型WTB无锁公头胶壳		页次 SHEET	1/1
			.X±0.20		核准 APPROVAL	JADE			客户料号 CUTM.NO.				
			.XX±0.10		单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)				