






技术指标:


1. 零件表面应光滑、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -25°C~85°C.
3. 额定电压: 0.5A
4. 额定电压: 50V. AC.
5. 接触电阻: 50mΩ MAX.
6. 绝缘电阻: 500MΩ Min.
7. 耐电压: 150V AC/1Minute



序号	品名	材质
1	0.5Pitch-40Pin(H=2.55)	LCP UL94V-0 阻燃
2	0.5Pitch-40Pin(H=2.55)	LCP UL94V-0 阻燃
3	0.5Pitch-40Pin(H=2.55)	铜合金/表面镀金
4	0.5Pitch-40Pin(H=2.55)	铜合金/表面镀金

SECTION A-A
SCALE 1:1

P/N	PIN	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F
FPC12-Q0.5-5ABRH255	5	7.45	3.07	2.00	7.10	4.60	4.50
FPC12-Q0.5-6ABRH255	6	7.95	3.57	2.50	7.60	5.10	5.00
FPC12-Q0.5-7ABRH255	7	8.45	4.07	3.00	8.10	5.60	5.50
FPC12-Q0.5-8ABRH255	8	8.95	4.57	3.50	8.60	6.10	6.00
FPC12-Q0.5-9ABRH255	9	9.45	5.07	4.00	9.10	6.60	6.50
FPC12-Q0.5-10ABRH255	10	9.95	5.57	4.50	9.60	7.10	7.00
FPC12-Q0.5-11ABRH255	11	10.45	6.07	5.00	10.10	7.60	7.50
FPC12-Q0.5-12ABRH255	12	10.95	6.57	5.50	10.60	8.10	8.00
FPC12-Q0.5-13ABRH255	13	11.45	7.07	6.00	11.10	8.60	8.50
FPC12-Q0.5-14ABRH255	14	11.95	7.57	6.50	11.60	9.10	9.00
FPC12-Q0.5-15ABRH255	15	12.45	8.07	7.00	12.10	9.60	9.50
FPC12-Q0.5-16ABRH255	16	12.95	8.57	7.50	12.60	10.10	10.00
.....							
FPC12-Q0.5-76ABRH255	76	42.95	38.57	37.50	42.60	40.10	40.00
FPC12-Q0.5-77ABRH255	77	43.45	39.07	38.00	43.10	40.60	40.50
FPC12-Q0.5-78ABRH255	78	43.95	39.57	38.50	43.60	41.10	41.00
FPC12-Q0.5-79ABRH255	79	44.45	40.07	39.00	44.10	41.60	41.50
FPC12-Q0.5-80ABRH255	80	44.95	40.57	39.50	44.60	42.10	42.00



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd		
TOLERANCE UNLESS OTHERWISE SPECIFIED				
.X±0.5	X.*±0.05	APR. Alex	TITLE: 0.5 Pitch 连接器 (H=2.55)	
.XX±0.2	.X.*±1	CHK. Jack	DWG NO. FPC12-Q0.5-NABRH255	
.XXX±0.1	.XX.*±	DRA. Can	PROJ.	CUSTOMER DRAWING
SIZE A4	SCALE 1:1	SHEET 1/1	REV. A	