





SPECIFICATION:




- MATERIAL & FINISH:SEE THE LIST;
- PLATING SPECIFICATION:
 - CONTACTS:

Ni 50u" MIN. UNDER PLATED OVER ALL.
Au PLATED ON THE MATING AREA OF CONTACT.
Au PLATED ON THE SOLDER AREA.
 - SHELL:Ni 30u" MIN. UNDER PLATED OVER ALL.
 - MID PLATE:CLEAR ONLY
- MECHANICAL:
 - MATING FORCE:0.5~2.0kgf;
 - UNMATING FORCE:0.8~2.0kgf.
0.6~2.0kgf AFTER DURABILITY TEST;
 - DURABILITY:10000 CYCLES;
- ELECTRICAL:
 - CURRENT RATING:5A Max;
 - VOLTAGE RATING:20V Max;
 - DIELECTRIC WITHSTANDING VOLTAGE:100Vac;
 - CONTACT RESISTANCE:40mΩ Ohms Max.;
 - INSULATION RESISTANCE:100M Ohms Min.;
- ENVIRONMENTAL:
 - OPERATING TEMPERATURE:
-40°C~+85°C;
 - WETTING TEMPERATURE:
265±5°C,5±0.5s
 - Salt Spray Test:48H Min

PIN DEFINE TABLE			
PIN	SIGNAL	PIN	SIGNAL
A12	GND	B1	GND
A11	-	B2	-
A10	-	B3	-
A9	VBUS	B4	VBUS
A8	SBU1	B5	CC2
A7	D-	B6	D+
A6	D+	B7	D-
A5	CC1	B8	SBU2
A4	VBUS	B9	VBUS
A3	-	B10	-
A2	-	B11	-
A1	GND	B12	GND

NO.	PART NAME	Q'TY	MATERIAL	FINISH
5	CAP	1	High temperature plastic	UL94 V-0,Black
4	Shell	1	Stainless Steel,T=0.30mm	30u"Ni Min.
3	GroundBar	1	Stainless Steel,T=0.15mm	No Plating
2	Contact	16	Copper Alloy,T=0.15mm	Au/Ni-Plated
1	Housing	1	High temperature plastic	UL94 V-0 ORANGE

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-TYPE-C-069		版本 REV.	A
			X.±0.50	X.*±5°	审核 CHECK	EVA			品名 TITLE	TYPE-C 16p 立式插座H8.8mm		页次 SHEET	1/1
			.X±0.35	.X.*±3°	核准 APPROVAL	JADE			客户料号 CUTM.NO.				
			.XX±0.25	.XX.*±2.5°	单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)				



说明:

1. 每卷前后各空 10PCS, 尾部用美纹胶纸封住;
2. 将产品放满盘后, 再卷一圈保护带, 用美纹胶纸将其封住, 并贴上 1Pcs 物料标签;
3. 每 10 卷盘一叠共 3500Pcs 并装入 1 个外箱内;
4. 在搬运过程中要轻拿轻放;
5. 在运输中不可堆放过多 (1.8M 最高), 不可重压;
6. 跌落测试条件:

成品箱从 1.2 米高度自由落体 (一角三棱六面):

- a. 产品不可跑出下带凹槽;
- b. 产品不可有摔伤, 变形;
- c. 内包装材料不可严重破损.

NO.	NAME	SPEC	Q'TY
0	TYPE C RECEPTACLE		3500PCS/CARTON
1	CARRIER TAPE	W=24mm,T=0.50mm	350PCS/PLATE
2	COVER TAPE	W=21.3mm	10PLATES/CARTON
3	REEL PLATE	φ330*100*24.4mm	10PCS/CARTON
4	RoHS LABEL		10PCS/CARTON
5	PRODUCT LABER		10PCS/CARTON
6	CARTON	350*340*310mm	1PCS/PACKAGE

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-TYPE-C-069	版本 REV.	A
			X.±0.50	X.*±5°	审核 CHECK	EVA			品名 TITLE	TYPE-C 16p 主触点间距H8.8mm	页次 SHEET	1/1
			.X±0.35	.X'*±3°	核准 APPROVAL	JADE			客户料号 CUTM.NO.			
			.XX±0.25	.XX'*±2.5°	单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)			