











PIN DEFINE TABLE			
PIN	SIGNAL	PIN	SIGNAL
A12	GND	B1	GND
A11	-	B2	-
A10	-	B3	-
A9	VBUS	B4	VBUS
A8	SBU1	B5	CC2
A7	D-	B6	D+
A6	D+	B7	D-
A5	CC1	B8	SBU2
A4	VBUS	B9	VBUS
A3	-	B10	-
A2	-	B11	-
A1	GND	B12	GND

SPECIFICATION:

1. MATERIAL & FINISH:SEE THE LIST;

2. PLATING SPECIFICATION:

2-1.CONTACTS:

Ni 50u" MIN. UNDER PLATED OVER ALL.

Au PLATED ON THE MATING AREA OF CONTACT.

Au PLATED ON THE SOLDER AREA.

2-2.SHELL:Ni 30u" MIN. UNDER PLATED OVER ALL.

2-3.MID PLATE:CLEAR ONLY

3. MECHANICAL:

3.1.MATING FORCE:0.5~2.0kgf;

3.2.UNMATING FORCE:0.8~2.0kgf.

0.6~2.0kgf AFTER DURABILITY TEST;

3.3.DURABILITY:10000 CYCLES;

4.ELECTRICAL:

4.1.CURRENT RATING:5A Max;

4.2.VOLTAGE RATING:20V Max;

4.3.DIELECTRIC WITHSTANDING VOLTAGE:100VAc;

4.4.CONTACT RESISTANCE:40mΩ Ohms Max.;

4.5.INSULATION RESISTANCE:100M Ohms Min.;


5.ENVIRONMENTAL:






5.1.OPERATING TEMPERATURE:-40°C~+85°C;

5.2.WETTING TEMPERATURE:265±5°C,5±0.5s

5.3.Salt Spray Test:48H Min

NO.	PART NAME	Q'TY	MATERIAL	FINISH
4	Shell	1	Stainless Steel,T=0.30mm	30u"Ni Min.
3	GroundBar	1	Stainless Steel,T=0.15mm	No Plating
2	Contact	14	Copper Alloy,T=0.15mm	Au/Sn/Ni-Plated
1	Housing	1	High temperature plastic	UL94 V-0 Orange

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-TYPE-C-057	版本 REV.	A
			X.:±0.50	X.:±5°	审核 CHECK	LEO			品名 TITLE	TYPE-C 16P直立式 DIP型 间距 H10.0mm	页次 SHEET	1/1
			X.X:±0.35	X.X:±3°	核准 APPROVAL	JOHN			客户料号 CUTM.NO.			
			X.XX:±0.25	X.XX:±2.5°	单位 UNITS	MM	比例 SCALE	1:1	 兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.			



说明:

1. 每卷前后各空10PCS,尾部用美纹胶纸封住;
2. 将产品放满盘后,再卷一圈保护带,用美纹胶纸将其封住,并贴上1Pcs物料标签;
3. 每10卷盘一叠共3000Pcs并装入1个外箱内;
4. 在搬运过程中要轻拿轻放;
5. 在运输中不可堆放过多(1.8M最高),不可重压;
6. 跌落测试条件:

成品箱从1.2米高度自由落体(一角三棱六面):

- a. 产品不可跑出下带凹槽;
- b. 产品不可有摔伤,变形;
- c. 内包装材料不可严重破损.

NO.	NAME	SPEC	Q'TY
0	TYPE C RECEPTACLE		2500PCS/CARTON
1	CARRIER TAPE	W=24mm,T=0.50mm	250PCS/PLATE
2	COVER TAPE	W=21.3mm	10PLATES/CARTON
3	REEL PLATE	ø330*100*24.4mm	10PCS/CARTON
4	RoHS LABEL		10PCS/CARTON
5	PRODUCT LABER		10PCS/CARTON
6	CARTON	350*340*310mm	1PCS/PACKAGE

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-TYPE-C-057		版本 REV.	A
			X.:±0.50	X.:±5°	审核 CHECK	LEO			品名 TITLE	TYPE-C 16P直立式 DIP型 间距 H10.0mm		页次 SHEET	1/1
			X.X:±0.35	X.X:±3°	核准 APPROVAL	JOHN			客户料号 CUTM.NO.				
			X.XX:±0.25	X.XX:±2.5°	单位 UNITS	MM	比例 SCALE	1:1	 兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.				