




A		B		C		D		E	
REV.		DESCRIPTION		ECN NO.		NAME		DATE	




1

2

3


4

5



15 SHEAF/CARTON

A SHEAF
20 TUBES



NO.	NAME	SPEC	Q'TY
1	TYPE C PLUG(NO PCB)		18000PCS/CARTON
2	TUBE	PVC,530*13.5*4.4mm	20*15=300PCS/CARTON
3	STUFF	RUBBER,11*12.7*4.8mm	2*300=600PCS/CARTON
4	CARTON	CORRUGATED BOARD,A=B 570*270*120mm	1PCS/PACKAGE

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					BXCONN®		
DIM. TOL. x. ±0.50 x.x ±0.35 x.xx ±0.25 GENERAL ANGLE: x.° ±5.0° x.x° ±3.0° x.xx° ±2.5°		TITLE: Type-C Plug 12Pin T3.2拉伸 外壳有弹片							
DWG. NO.: UC03-OB12F10N10			CHECKED: MAX						
PART NO.: UC03-OB12F10N10			DRAWN: ELLA						
UNIT: mm			SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn			APPROVED: WILL
									