





SECTION A-A
SCALE 1:1




- 技术指标:
1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
 2. 温度范围: -25°C~85°C.
 3. 额定电流: 0.5A
 4. 额定电压: 50V, AC.
 5. 接触电阻: 50mΩ MAX.
 6. 绝缘电阻: 500MΩ Min.
 7. 耐压: 150V AC/1Minute



通用扁平线(Applicable Flat Cable)

P/N	PIN	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F
BX-FC05-FWK-H255-5P	5	7.45	3.07	2.00	7.10	4.60	4.50
BX-FC05-FWK-H255-6P	6	7.95	3.57	2.50	7.60	5.10	5.00
BX-FC05-FWK-H255-7P	7	8.45	4.07	3.00	8.10	5.60	5.50
BX-FC05-FWK-H255-8P	8	8.95	4.57	3.50	8.60	6.10	6.00
BX-FC05-FWK-H255-9P	9	9.45	5.07	4.00	9.10	6.60	6.50
BX-FC05-FWK-H255-10P	10	9.95	5.57	4.50	9.60	7.10	7.00
BX-FC05-FWK-H255-11P	11	10.45	6.07	5.00	10.10	7.60	7.50
BX-FC05-FWK-H255-12P	12	10.95	6.57	5.50	10.60	8.10	8.00
BX-FC05-FWK-H255-13P	13	11.45	7.07	6.00	11.10	8.60	8.50
BX-FC05-FWK-H255-14P	14	11.95	7.57	6.50	11.60	9.10	9.00
BX-FC05-FWK-H255-15P	15	12.45	8.07	7.00	12.10	9.60	9.50
BX-FC05-FWK-H255-16P	16	12.95	8.57	7.50	12.60	10.10	10.00
.....							
BX-FC05-FWK-H255-76P	76	42.95	38.57	37.50	42.60	40.10	40.00
BX-FC05-FWK-H255-77P	77	43.45	39.07	38.00	43.10	40.60	40.50
BX-FC05-FWK-H255-78P	78	43.95	39.57	38.50	43.60	41.10	41.00
BX-FC05-FWK-H255-79P	79	44.45	40.07	39.00	44.10	41.60	41.50
BX-FC05-FWK-H255-80P	80	44.95	40.57	39.50	44.60	42.10	42.00



适用线路板(PCB LAYOUT)

序号	品名	材质	制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	料号 PART NO.		版本 REV.	A
1	0.5mm间距式带扣胶芯(H=2.55)	LCP UL94V-0 本色				X.±0.50	±1°		品名 TITLE	BX-FC05-FWK-H255-NP	页次 SHEET	1/1
2	0.5mm间距式后盖带扣(H=2.55)	LCP UL94V-0 黑色				.X±0.20		审核 CHECK	客户料号 CUTM.NO.			
3	0.5mm间距式端子带扣(H=2.55)	铜合金/表面镀金				.XX±0.10		核准 APPROVAL	 Bossie (博锡)			
4	0.5mm间距式焊片带扣(H=2.55)	铜合金/表面镀锡						单位 UNITS				
								MM	比例 SCALE	1:1		