



5.3.Salt Spray Test:48H Min

NO.	PART NAME	Q'TY	MATERIAL	FINISH
5	CAP	1	High temperature plastic	UL94 V-0,Black
4	Shell	1	Stainless Steel,T=0.30mm	30u"Ni Min.
3	GroundBar	1	Stainless Steel,T=0.15mm	No Plating
2	Contact	16	Copper Alloy,T=0.15mm	Au/Ni-Plated
1	Housing	1	High temperature plastic	UL94 V-0

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.50	.X°± 5°	APR. Alex	TITLE: TYPE-C 16p 插拔力H8.8mm		
.XX±0.35	.X°± 3°	CHK. Jack	DWG NO. TYPE-C-F27-2TDWH88-X		
.XXX±0.25	.XX°± 2.5	DRA. Can	PROJ. 		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1/1



- 说明:
- 1.每卷前后各空10PCS,尾部用美纹纸封住;
 - 2.将产品放满盘后,再卷一圈保护带,用美纹纸将其封住,并贴上1Pcs物料标签;
 - 3.每10卷盘一叠共3500Pcs并装入1个外箱内;
 - 4.在搬运过程中要轻拿轻放;
 - 5.在运输中不可堆放过高(1.8M最高),不可重压;
 - 6.跌落测试条件:
成品箱从1.2米高度自由落体(一角三棱六面):
a.产品不可跳出下带凹槽;
b.产品不可有摔伤,变形;
c.内包装材料不可严重破损。

				DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd				
NO.	NAME	SPEC	Q'TY	TOLERANCE UNLESS OTHERWISE SPECIFIED						
0	TYPE C RECEPTACLE		3500PCS/CARTON	.X±0.50	.X°± 5°	APR.	Alex	TITLE: TYPE-C 主触点间距H8.8mm——包塑铜		
1	CARRIER TAPE	W=24mm,T=0.50mm	350PCS/PLATE			CHK.	Jack	DWG NO. TYPE-C-F27-2TDWH88-X		
2	COVER TAPE	W=21.3mm	10PLATES/CARTON	.XX±0.35	.X°± 3°	DRA.	Can	PROJ.		CUSTOMER DRAWING
3	REEL PLATE	ø330*100*24.4mm	10PCS/CARTON					SIZE A4	SCALE 1:1	SHEET 1 / 1
4	RoHS LABEL		10PCS/CARTON	.XXX±0.25	.XX°± 2.5					
5	PRODUCT LABER		10PCS/CARTON							
6	CARTON	350*340*310mm	1PCS/PACKAGE							