





技术要求:

- 1.表面不能有明显外观问题.
- 2.先打铜底0.5—1um,镀镍2—2.5um,镀哑锡3—5um.
- 3.额定电流:60A
- 4.螺纹扭矩:13 lbf.in
- 5.材质:H62



PCB.WELDING DRAWING (TOLERANCE:±0.05)

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					BXCONN®	
DIM. TOL. .x ±0.30 .xx ±0.25 .xxx ±0.15 GENERAL ANGLE: .x° ±5° .xx° ±1°		TITLE: PCB SOLDERING TERMINAL						
DWG. NO.: T-1192M5					CHECKED: MAX			
PART NO.: T-1192M5					DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn		