











PIN DEFINE TABLE			
PIN	SIGNAL	PIN	SIGNAL
A12	GND	B1	GND
A11	—	B2	—
A10	—	B3	—
A9	VBUS	B4	VBUS
A8	SBU1	B5	CC2
A7	D—	B6	D+
A6	D+	B7	D—
A5	CC1	B8	SBU2
A4	VBUS	B9	VBUS
A3	—	B10	—
A2	—	B11	—
A1	GND	B12	GND

SPECIFICATION:

1. MATERIAL & FINISH:SEE THE LIST;
2. PLATING SPECIFICATION:

2-1.CONTACTS:

Ni 50u" MIN. UNDER PLATED OVER ALL.
Au PLATED ON THE MATING AREA OF CONTACT.
Au PLATED ON THE SOLDER AREA.

2-2.SHELL:Ni 30u" MIN. UNDER PLATED OVER ALL.

2-3.MID PLATE:CLEAR ONLY

3. MECHANICAL:

- 3.1.MATING FORCE:0.5~2.0kgf;
- 3.2.UNMATING FORCE:0.8~2.0kgf.
0.6~2.0kgf AFTER DURABILITY TEST;
- 3.3.DURABILITY:10000 CYCLES;



4.ELECTRICAL:




- 4.1.CURRENT RATING:5A Max;
- 4.2.VOLTAGE RATING:20V Max;
- 4.3.DIELECTRIC WITHSTANDING VOLTAGE:100VAc;
- 4.4.CONTACT RESISTANCE:40mΩ Ohms Max.;
- 4.5.INSULATION RESISTANCE:100M Ohms Min.;

5.ENVIRONMENTAL:


- 5.1.OPERATING TEMPERATURE:−40°C~+85°C;
- 5.2.WETTING TEMPERATURE:265±5°C,5±0.5s
- 5.3.Salt Spray Test:48H Min

NO.	PART NAME	Q'TY	MATERIAL	FINISH
4	Shell	1	Stainless Steel,T=0.30mm	30u"Ni Min.
3	GroundBar	1	Stainless Steel,T=0.15mm	No Plating
2	Contact	14	Copper Alloy,T=0.15mm	Au/Sn/Ni-Plated
1	Housing	1	High temperature plastic	UL94 V-0 Orange

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-TYPE-C-057	版本 REV.	A
			X.±0.50	X'±5°	审核 CHECK	EVA			品名 TITLE	TYPE-C 16P直立式 DIP型 母座 H10.0mm	页次 SHEET	1/1
			.X±0.35	.X"±3°	核准 APPROVAL	JADE			客户料号 CUTM.NO.			
			.XX±0.25	.XX"±2.5°	单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)			



NO.	NAME	SPEC	Q'TY
0	TYPE C RECEPTACLE		2500PCS/CARTON
1	CARRIER TAPE	W=24mm,T=0.50mm	250PCS/PLATE
2	COVER TAPE	W=21.3mm	10PLATES/CARTON
3	REEL PLATE	ø330*100*24.4mm	10PCS/CARTON
4	RoHS LABEL		10PCS/CARTON
5	PRODUCT LABER		10PCS/CARTON
6	CARTON	350*340*310mm	1PCS/PACKAGE

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-TYPE-C-057	版本 REV.	A
			X.±0.50	X°.±5°	审核 CHECK	EVA			品名 TITLE	TYPE-C 16P直立式 DIP型 厚度 H10.0mm	页次 SHEET	1/1
			.X±0.35	.X°.±3°	核准 APPROVAL	JADE			客户料号 CUTM.NO.			
			.XX±0.25	.XX°.±2.5°		单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)		

说明:

- 1.每卷前后各空10PCS,尾部用美纹胶纸封住;
- 2.将产品放满盘后,再卷一圈保护带,用美纹胶纸将其封住,并贴上1Pcs物料标签;
- 3.每10卷盘一叠共3000Pcs并装入1个外箱内;
- 4.在搬运过程中要轻拿轻放;
- 5.在运输中不可堆放过多(1.8M最高),不可重压;
- 6.跌落测试条件:

成品箱从1.2米高度自由落体(一角三棱六面):

- a.产品不可跑出下带凹槽;
- b.产品不可有摔伤,变形;
- c.内包装材料不可严重破损.