







技术指标:
1.温度范围Temperatuer Range: -40°C~125°C.
2.额定电压Voltage Rating: 125V AC,DC.
3.耐电压Dielectric Strength: 1000V AC/minute.
4.接触电阻Contact Resistance: ≤20mΩ
5.绝缘电阻Insulation esistance: ≥100MΩ.
6.额定电流Current Rating: 3A AC,DC(AWG22#).
7.适用线径Applicable wire
insulation: AWG22#-26#, OD1.4mmMax

P/N	PIN	DIM A	DIM B	DIM C
BX-MX2.0-2PJK-S	2	2.00	8.00	6.00
BX-MX2.0-3PJK-S	3	4.00	10.00	8.00
BX-MX2.0-4PJK-S	4	6.00	12.00	10.00
BX-MX2.0-5PJK-S	5	8.00	14.00	12.00
BX-MX2.0-6PJK-S	6	10.00	16.00	14.00
BX-MX2.0-7PJK-S	7	12.00	18.00	16.00
BX-MX2.0-8PJK-S	8	14.00	20.00	18.00
BX-MX2.0-9PJK-S	9	16.00	22.00	20.00
BX-MX2.0-10PJK-S	10	18.00	24.00	22.00
BX-MX2.0-11PJK-S	11	20.00	26.00	24.00
BX-MX2.0-12PJK-S	12	22.00	28.00	26.00
BX-MX2.0-13PJK-S	13	24.00	30.00	28.00
BX-MX2.0-14PJK-S	14	26.00	32.00	30.00
BX-MX2.0-15PJK-S	15	28.00	34.00	32.00

1	MX2.0 B型WTB带锁公头胶壳	PBT/白色
序号	名称	材质

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING
			X.±0.50	±1°	审核 CHECK
			.X±0.20		核准 APPROVAL
			.XX±0.10		单位 UNITS

EMMA	比例 SCALE	1:1
EVA	MM	
JADE		

料号 PART NO.	BX-MX2.0-NPJK-S	版本 REV.	A
品名 TITLE	MX2.0 B型WTB带锁公头胶壳	页次 SHEET	1/1
客户料号 CUTM.NO.			