






PCB.WELDING DRAWING (TOLERANCE:±0.05)

技术要求:

- 1.打铜底 $0.5-1\mu\text{m}$ ,镍 $2-2.5\mu\text{m}$ ,镀零锡 $3-5\mu\text{m}$ 2.铆好后不得有松动现象.
- 2.插脚尖部符合可焊性要求.
- 3.螺纹需符合通止规/止针要求.
- 4.螺纹扭矩: $0.6\text{Nm}$ .
- 5.额定电流: 30A.

|                                      |         |                                                           |                                                                                             |                  |             |
|--------------------------------------|---------|-----------------------------------------------------------|---------------------------------------------------------------------------------------------|------------------|-------------|
| DIMENSION IN mm                      |         | 厦门市辛译精密电子有限公司<br>Xiamen XinYi Xyeconn Electronics Co.,Ltd |                                                                                             |                  |             |
| TOLERANCE UNLESS OTHERWISE SPECIFIED |         |                                                           |                                                                                             |                  |             |
| X.X±0.30                             | X.*±5°  | APR.<br>Alex                                              | TITLE: PCB SOLDERING TERMINAL                                                               |                  |             |
| X.XX±0.25                            | X.X*±1° | CHK.<br>Jack                                              | DWG NO. XY-M34-02                                                                           |                  |             |
| X.XXX±0.15                           |         | DRA.<br>Can                                               | PROJ.  | CUSTOMER DRAWING |             |
|                                      |         |                                                           | SIZE A4                                                                                     | SCALE 1:1        | SHEET 1 / 1 |
|                                      |         |                                                           |                                                                                             | REV. A           |             |