







A B C D E F G




NOTES:
 1. RATING: 12VDC 50mA
 2. CONTACT RESISTANCE: 100mΩ Max
 3. INSULATION RESISTANCE: 100MΩ 250VDC FOR 1MIN
 4. DIELECTRIC STRENGTH: 250VAC(50/60Hz) FOR 1MIN
 5. LIFE TEST: 100,000 CYCLES
 6. OPERATION FORCE&TRAVEL: SEE SPECIFICATION



CIRCUIT



P.C.B LAYOUT



ITEM	PART NAME	MATERIAL
6		
5	TERMINAL	Bronze Silver Plated
4	CONTACT	ABS
3	LED	GaAsP/GaP
2	BUTTON	POM
1	HOUSING	PBT

A4				
A3				
A2				
A1		ABS		
REV	DATE	REVISION DESCRIPTION	ISSUE	

台普
ROCPU

COMMON TOLERANCE

X.XX ± 0.10

X.X ± 0.15

X ± 0.25

ANGULAR —

UNIT

MM

PROJCTED



PRODUCT NAME:
MODEL NO: TPB01-103L1B7

DRAWN BY

FUYUAN

CHECKED BY

COCO

DATE

2019

APPROVAL

ALEN

ROCPU TECHNOLOGY CO., LTD

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission

A

D

E

F

G