














1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围： $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压： $50\text{V} / \text{DC}$
4. 额定电流： $0.5\text{A} / \text{AC}$
5. 接触电阻： $\leq 0.03\Omega$ 。
6. 绝缘电阻： $\geq 100\text{M}\Omega$






P/N	PIN	DIM A	DIM B	DIM C
BX-FC05-FWK-H22-5P	5	2.00	7.50	4.40
BX-FC05-FWK-H22-6P	6	2.50	8.00	4.90
BX-FC05-FWK-H22-7P	7	3.00	8.50	5.40
BX-FC05-FWK-H22-8P	8	3.50	9.00	5.90
BX-FC05-FWK-H22-9P	9	4.00	9.50	6.40
BX-FC05-FWK-H22-10P	10	4.50	10.00	6.90
BX-FC05-FWK-H22-11P	11	5.00	10.50	7.40
BX-FC05-FWK-H22-12P	12	5.50	11.00	7.90
BX-FC05-FWK-H22-13P	13	6.00	11.50	8.40
BX-FC05-FWK-H22-14P	14	6.50	12.00	8.90
BX-FC05-FWK-H22-15P	15	7.00	12.50	9.40
BX-FC05-FWK-H22-16P	16	7.50	13.00	9.90
*****	*****	*****	*****	*****
BX-FC05-FWK-H22-47P	47	23.00	28.50	25.40
BX-FC05-FWK-H22-48P	48	23.50	29.00	25.90
BX-FC05-FWK-H22-49P	49	24.00	29.50	26.40
BX-FC05-FWK-H22-50P	50	24.50	30.00	26.90
BX-FC05-FWK-H22-51P	51	25.00	30.50	27.40

序号	品名	材质	制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-FC05-FWK-H22-NP		版本 REV.	A		
1	0.5掀盖带扣胶芯(H2.2)	LCP UL94V-0 本色				X.±0.50	±1°	审核	EVA			品名 TITLE	Φpin数 0.5 Pitch掀盖带扣(H=2.2)		页次 SHEET	1/1		
2	0.5掀盖带扣端子(H2.2)	磷铜/表面镀锡				.X±0.20		核准	JADE			客户料号 CUTM.NO.						
3	0.5掀盖带扣后盖(H2.2)	LCP UL94V-0 黑色				.XX±0.10		单位 UNITS	MM	比例 SCALE	1:1							
4	0.5掀盖带扣焊片(H2.2)	磷铜/表面镀锡																



- 技术指标:
1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
 2. 温度范围: -25°C~85°C.
 3. 额定电压: 50V /DC
 4. 额定电流: 0.5A /AC
 5. 接触电阻: ≤0.03Ω.
 6. 绝缘电阻: ≥100MΩ



P/N	PIN	DIM A	DIM B	DIM C
BX-FC05-FWK-H22-52P	52	25.50	31.00	27.90
BX-FC05-FWK-H22-53P	53	26.00	31.50	28.40
BX-FC05-FWK-H22-54P	54	26.50	32.00	28.90
BX-FC05-FWK-H22-55P	55	27.00	32.50	29.40
BX-FC05-FWK-H22-56P	56	27.50	33.00	29.90
BX-FC05-FWK-H22-57P	57	28.00	33.50	30.40
BX-FC05-FWK-H22-58P	58	28.50	34.00	30.90
BX-FC05-FWK-H22-59P	59	29.00	34.50	31.40
BX-FC05-FWK-H22-60P	60	29.50	35.00	31.90
BX-FC05-FWK-H22-61P	61	30.00	35.50	32.40
BX-FC05-FWK-H22-62P	62	30.50	36.00	32.90
BX-FC05-FWK-H22-63P	63	31.00	36.50	33.40
.....				
BX-FC05-FWK-H22-92P	92	45.50	51.00	47.90
BX-FC05-FWK-H22-93P	93	46.00	51.50	48.40
BX-FC05-FWK-H22-94P	94	46.50	52.00	48.90
BX-FC05-FWK-H22-95P	95	47.00	52.50	49.40
BX-FC05-FWK-H22-96P	96	47.50	53.00	49.90

序号	品名	材质	制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-FC05-FWK-H22-NP	版本 REV.	A
1	0.5掀盖带扣胶芯(H2.2)	LCP UL94V-0 本色				X.±0.50	±1°	审核 CHECK	EVA		品名 TITLE	Apin 0.5 Pitch 掀盖带扣(H=2.2)	页次 SHEET	1/1
2	0.5掀盖带端子(H2.2)	磷铜/表面镀锡				.X±0.20		核准 APPROVAL	JADE		客户料号 CUTM.NO.			
3	0.5掀盖带扣后盖(H2.2)	LCP UL94V-0 黑色				.XX±0.10		单位 UNITS	MM	比例 SCALE	1:1			
4	0.5掀盖带扣焊片(H2.2)	磷铜/表面镀锡												