






技术要求:

- 1.表面不能有明显外观问题.
- 2.先打铜底0.5—1um,镀镍2—2.5um,镀哑锡3—5um.
- 3.额定电流:60A
- 4.螺纹扭矩:13 lbf.in
- 5.材质:H62



PCB.WELDING DRAWING (TOLERANCE:±0.05)

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-T5-004		版本 REV.	A
			.X±0.30	X.*±5°					品名 TITLE	PCB SOLDERING TERMINAL		页次 SHEET	1/1
			.XX±0.25	.X*±1°					客户料号 CUTM.NO.				
			.XXX±0.15										
					核准 APPROVAL	JADE							
					单位 UNITS	MM	比例 SCALE	1:1	Bossie (博锡)				