










P/N	PIN	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F
FPC13-YZ0.5-5ABRH54	5	2.00	3.06	6.00	4.40	2.50	4.00
FPC13-YZ0.5-6ABRH54	6	2.50	3.56	6.50	4.90	3.00	4.50
FPC13-YZ0.5-7ABRH54	7	3.00	4.06	7.00	5.40	3.00	5.00
FPC13-YZ0.5-8ABRH54	8	3.50	4.56	7.50	5.90	4.00	5.50
FPC13-YZ0.5-9ABRH54	9	4.00	5.06	8.00	6.40	4.00	6.00
FPC13-YZ0.5-10ABRH54	10	4.50	5.56	8.50	6.90	4.00	6.50
FPC13-YZ0.5-11ABRH54	11	5.00	6.06	9.00	7.40	4.00	7.00
FPC13-YZ0.5-12ABRH54	12	5.50	6.56	9.50	7.90	4.00	7.50
FPC13-YZ0.5-13ABRH54	13	6.00	7.06	10.00	8.40	4.00	8.00
FPC13-YZ0.5-14ABRH54	14	6.50	7.56	10.50	8.90	4.00	8.50
FPC13-YZ0.5-15ABRH54	15	7.00	8.06	11.00	9.40	4.00	9.00
FPC13-YZ0.5-16ABRH54	16	7.50	8.56	11.50	9.90	4.00	9.50
.....							
FPC13-YZ0.5-56ABRH54	56	27.50	28.56	31.50	29.90	8.00	29.50
FPC13-YZ0.5-57ABRH54	57	28.00	29.06	32.00	30.40	8.00	30.00
FPC13-YZ0.5-58ABRH54	58	28.50	29.56	32.50	30.90	8.00	30.50
FPC13-YZ0.5-59ABRH54	59	29.00	30.06	33.00	31.40	8.00	31.00
FPC13-YZ0.5-60ABRH54	60	29.50	30.56	33.50	31.90	8.00	31.50

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -25°C~85°C.
3. 额定电流: 0.5A
4. 额定电压: 50V. AC.
5. 接触电阻: <50mΩ MAX.
6. 绝缘电阻: >500MΩ Min.
7. 耐压: 150V AC/1Minute



序号	品名	材质
1	0.5 Pitch 立式插座(H=5.4)	LCP UL94V-0 本色
2	0.5 Pitch 立式插座(H=5.4)	LCP UL94V-0 黑色
3	0.5 Pitch 立式端子(H=5.4)	铜合金/表面镀金
4	0.5 Pitch 立式端子(H=5.4)	铜合金/表面镀镍

DIMENSION IN mm

TOLERANCE UNLESS OTHERWISE SPECIFIED

.X±0.5	X.*±0.05
.XX±0.2	.X.*±1
.XXX±0.1	.XX.*±

厦门市辛译精密电子有限公司
Xiamen XinYi Xyecom Electronics Co.,Ltd

APR. Alex	TITLE: 0.5 Pitch 立式插座(H=5.4) 总图
CHK. Jack	DWG NO. FPC13-YZ0.5-NABRH54
DRA. Can	PROJ. CUSTOMER DRAWING
SIZE A4	SCALE 1:1
SHEET 1/1	REV. A