









NOTES:

1.MECHANICAL:MATING FORCE: 5-20N .

UNMATING FORCE: 8-20N .

DURABILITY: 10000 CYCLES MIN.

2.ELECTRICAL:

CURRENT: 5.0A MAX

VOLTAGE: 20V MAX

WITHSTANDING VOLTAGE: 100V AC

CONTACT RESISTANCE: 40 mΩ MAX INITIAL;


50 mΩ MAX AFTER 10000 CYCLES

3.ENVIRONMENTAL:

OPERATING TEMPERATURE RANGE -30°C ~ +80°C

4.Salt Spray:24H

8.34^{+0.06}_{-0.02}



BOM

名称	材料规格
主体	LCP 黑色 端子C2680 T=0.15mm 全1u” 卡勾:SUS301 H T=0.15mm 素材
外壳	SUS201 1/4H T=0.30mm 亮Ni:80u”

A1	GND	B12	GND
A2	-	B11	-
A3	-	B10	-
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	-	B3	-
A11	-	B2	-
A12	GND	B1	GND

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-TYPE-C-520	版本 REV.	A
			X.±0.50	X.*±5°	审核 CHECK	EVA			品名 TITLE	Type-C 16Pin 板L型 L=8.35	页次 SHEET	1/1
			.X±0.35	.X.*±3°	核准 APPROVAL	JADE			客户料号 CUTM.NO.			
			.XX±0.25	.XX.*±2.5°	单位 UNITS	MM	比例 SCALE	1:1	Bossie (博锡)			

