







技术指标(Technical Index):


- 1.工作温度(Temperature range): $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):100V DC/AC(rms).
- 3.额定电流(Rated current):2.0A.
- 4.接触电阻(Contact resistance): $\leq 40\text{m}\Omega$.
- 5.耐压值(Dielectricwithstanding voltage):
500V AC/minute.
- 6.绝缘电阻(Insulation resistance): $\geq 500\text{M}\Omega$.
- 7.适用线规(Apply to gauge):AWG#24~#28. O.D.
1.28mm(MAX)



SECTION A-A



SECTION B-B



SECTION C-C

1	MX1.5 B型 WTB公头端子	磷青铜/镀亮锡
序号	名称	材质

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-MX1.5-DZ	版本 REV.	A
			X.±0.50	±1°	审核 CHECK	EVA			品名 TITLE	MX1.5 B型 WTB公头端子	页次 SHEET	1/1
			.X±0.20		核准 APPROVAL	JADE			客户料号 CUTM.NO.			
			.XX±0.10		单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)			