


PIN DEFINE TABLE								
PIN	A1	A4	A5	A6	A7	A8	A9	A12
SIGNAL	GND	VBUS	CC1	D+	D-	SBU1	VBUS	GND
PIN	B12	B9	B8	B7	B6	B5	B4	B1
SIGNAL	GND	VBUS	SBU2	D-	D+	CC2	VBUS	GND

SPECIFICATION:

- Material:
  - HOUSING&MOLDING:LCP,UL94 V-0
  - CONTACTS:COPPER ALLOY T=0.20mm
  - MIDDLE CLIP:SUS301-1/2H,T=0.15mm
  - SHELL:SUS, T=0.30mm
- Mechanical:
  - Mating force:5~20N;
  - Unmating force:6~20N;
  - Durability:10000 Cycles;
- Electrical:
  - Current Rating:3A/5A Max.;
  - Voltage Rating:20V Max.;
  - Dielectric Withstanding voltage:100VAc;
  - Contact resistance:40m Ohms Max.;
  - Insulation Resistance:100M Ohms Min.;
- Environmental:
  - Operating temperature:-40°C~+85°C;
  - Wetting Temperature:265±5°C,5±0.5s






(TOP VIEW)

RECOMMENDED P.C.B. LAYOUT (T:1.0~1.2mm)  
TOLERANCE UNSPECIFIED ±0.05mm

NO.	PART NAME	Q'TY	MATERIAL	FINISH
4	Shell	1	Stainless steel,T=0.30mm	30u"Ni Min.
3	GroundBar	1	Stainless steel,T=0.15mm	No Plating
2	Contact	16	Copper alloys,T=0.15mm	Au/Ni-Plated
1	Housing	1	High-temperature plastics	UL 94 V-0

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA	料号 PART NO.	版本 REV.	A	
			X.±0.30	X.*±5°						
			.X±0.35	.X*±3°	审核 CHECK	EVA	品名 TITLE	TYPE-C 16pin 母座板上型--全替	页次 SHEET	1/1
			.XX±0.25	.XX*±2.5°	核准 APPROVAL	JADE	客户料号 CUTM.NO.			
					单位 UNITS	MM	比例 SCALE	1:1		

**JB Bossie (博锡)**



说明:

1. 每卷前后各空16PCS,尾部用美纹胶纸封住;
2. 将产品放满盘后,再卷一圈保护带,用美纹胶纸将其封住,并贴上1Pcs物料标签;
3. 每10卷盘一叠共15000Pcs并装入1个外箱内;
4. 在搬运过程中要轻拿轻放;
5. 在运输中不可堆放过多(1.8M最高),不可重压;
6. 跌落测试条件:

成品箱从1.2米高度自由落体(一角三棱六面):

- a. 产品不可跑出下带凹槽;
- b. 产品不可有摔伤,变形;
- c. 内包装材料不可严重破损.

NO.	NAME	SPEC	Q'TY
0	TYPE C RECEPTACLE		15000PCS/CARTON
1	CARRIER TAPE	W=24mm,T=0.50mm	1500PCS/PLATE
2	COVER TAPE	W=21.5mm	10PLATES/CARTON
3	REEL PLATE	φ380*100*24.4mm	10PCS/CARTON
4	RoHS LABEL		10PCS/CARTON
5	PRODUCT LABELER		10PCS/CARTON
6	CARTON	390*390*310mm	1PCS/PACKAGE

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-TYPE-C-619		版本 REV.	A
			X.±0.30	X.'±5°	审核 CHECK	EVA		品名 TITLE	TYPE-C 16pin 母座板上型——全替		页次 SHEET	1/1
			.X±0.35	.X'±3°	核准 APPROVAL	JADE		客户料号 CUTM.NO.				
			.XX±0.25	.XX'±2.5°	单位 UNITS	MM	比例 SCALE	1:1				