

A			B		C		D		E																																																																																																																																																									
序号	品名	材质	技术指标:			REV.	DESCRIPTION	ECN NO.	NAME	DATE																																																																																																																																																								
1	0.5Pitch立式贴片(H=5.4)	LCP UL94V-0 本色	1.塑料表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。																																																																																																																																																															
	0.5Pitch立式后盖(H=5.4)	LCP UL94V-0 黑色	2.温度范围: -25°C~85°C.																																																																																																																																																															
	0.5Pitch立式端子(H=5.4)	铜合金/表面镀金	3.额定电流: 0.5A																																																																																																																																																															
	0.5Pitch立式焊片(H=5.4)	铜合金/表面镀锡	4.额定电压: 50V, AC.																																																																																																																																																															
			5.接触电阻: ≤50mΩ MAX.																																																																																																																																																															
			6.绝缘电阻: ≥500MΩ Min.																																																																																																																																																															
			7.耐电压: 150V AC/1Minute																																																																																																																																																															
2	适用扁平线(Applicable Flat Cable)																																																																																																																																																																	
3	<table><thead><tr><th>P/N</th><th>PIN</th><th>DIM A</th><th>DIM B</th><th>DIM C</th><th>DIM D</th><th>DIM E</th><th>DIM F</th></tr></thead><tbody><tr><td>FPC-0.5FZ-5PLBR-H54</td><td>5</td><td>2.00</td><td>3.06</td><td>6.00</td><td>4.40</td><td>2.50</td><td>4.00</td></tr><tr><td>FPC-0.5FZ-6PLBR-H54</td><td>6</td><td>2.50</td><td>3.56</td><td>6.50</td><td>4.90</td><td>3.00</td><td>4.50</td></tr><tr><td>FPC-0.5FZ-7PLBR-H54</td><td>7</td><td>3.00</td><td>4.06</td><td>7.00</td><td>5.40</td><td>3.00</td><td>5.00</td></tr><tr><td>FPC-0.5FZ-8PLBR-H54</td><td>8</td><td>3.50</td><td>4.56</td><td>7.50</td><td>5.90</td><td>4.00</td><td>5.50</td></tr><tr><td>FPC-0.5FZ-9PLBR-H54</td><td>9</td><td>4.00</td><td>5.06</td><td>8.00</td><td>6.40</td><td>4.00</td><td>6.00</td></tr><tr><td>FPC-0.5FZ-10PLBR-H54</td><td>10</td><td>4.50</td><td>5.56</td><td>8.50</td><td>6.90</td><td>4.00</td><td>6.50</td></tr><tr><td>FPC-0.5FZ-11PLBR-H54</td><td>11</td><td>5.00</td><td>6.06</td><td>9.00</td><td>7.40</td><td>4.00</td><td>7.00</td></tr><tr><td>FPC-0.5FZ-12PLBR-H54</td><td>12</td><td>5.50</td><td>6.56</td><td>9.50</td><td>7.90</td><td>4.00</td><td>7.50</td></tr><tr><td>FPC-0.5FZ-13PLBR-H54</td><td>13</td><td>6.00</td><td>7.06</td><td>10.00</td><td>8.40</td><td>4.00</td><td>8.00</td></tr><tr><td>FPC-0.5FZ-14PLBR-H54</td><td>14</td><td>6.50</td><td>7.56</td><td>10.50</td><td>8.90</td><td>4.00</td><td>8.50</td></tr><tr><td>FPC-0.5FZ-15PLBR-H54</td><td>15</td><td>7.00</td><td>8.06</td><td>11.00</td><td>9.40</td><td>4.00</td><td>9.00</td></tr><tr><td>FPC-0.5FZ-16PLBR-H54</td><td>16</td><td>7.50</td><td>8.56</td><td>11.50</td><td>9.90</td><td>4.00</td><td>9.50</td></tr><tr><td>.....</td><td>.....</td><td>.....</td><td>.....</td><td>.....</td><td>.....</td><td>.....</td><td>.....</td></tr><tr><td>FPC-0.5FZ-56PLBR-H54</td><td>56</td><td>27.50</td><td>28.56</td><td>31.50</td><td>29.90</td><td>8.00</td><td>29.50</td></tr><tr><td>FPC-0.5FZ-57PLBR-H54</td><td>57</td><td>28.00</td><td>29.06</td><td>32.00</td><td>30.40</td><td>8.00</td><td>30.00</td></tr><tr><td>FPC-0.5FZ-58PLBR-H54</td><td>58</td><td>28.50</td><td>29.56</td><td>32.50</td><td>30.90</td><td>8.00</td><td>30.50</td></tr><tr><td>FPC-0.5FZ-59PLBR-H54</td><td>59</td><td>29.00</td><td>30.06</td><td>33.00</td><td>31.40</td><td>8.00</td><td>31.00</td></tr><tr><td>FPC-0.5FZ-60PLBR-H54</td><td>60</td><td>29.50</td><td>30.56</td><td>33.50</td><td>31.90</td><td>8.00</td><td>31.50</td></tr></tbody></table>										P/N	PIN	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F	FPC-0.5FZ-5PLBR-H54	5	2.00	3.06	6.00	4.40	2.50	4.00	FPC-0.5FZ-6PLBR-H54	6	2.50	3.56	6.50	4.90	3.00	4.50	FPC-0.5FZ-7PLBR-H54	7	3.00	4.06	7.00	5.40	3.00	5.00	FPC-0.5FZ-8PLBR-H54	8	3.50	4.56	7.50	5.90	4.00	5.50	FPC-0.5FZ-9PLBR-H54	9	4.00	5.06	8.00	6.40	4.00	6.00	FPC-0.5FZ-10PLBR-H54	10	4.50	5.56	8.50	6.90	4.00	6.50	FPC-0.5FZ-11PLBR-H54	11	5.00	6.06	9.00	7.40	4.00	7.00	FPC-0.5FZ-12PLBR-H54	12	5.50	6.56	9.50	7.90	4.00	7.50	FPC-0.5FZ-13PLBR-H54	13	6.00	7.06	10.00	8.40	4.00	8.00	FPC-0.5FZ-14PLBR-H54	14	6.50	7.56	10.50	8.90	4.00	8.50	FPC-0.5FZ-15PLBR-H54	15	7.00	8.06	11.00	9.40	4.00	9.00	FPC-0.5FZ-16PLBR-H54	16	7.50	8.56	11.50	9.90	4.00	9.50									FPC-0.5FZ-56PLBR-H54	56	27.50	28.56	31.50	29.90	8.00	29.50	FPC-0.5FZ-57PLBR-H54	57	28.00	29.06	32.00	30.40	8.00	30.00	FPC-0.5FZ-58PLBR-H54	58	28.50	29.56	32.50	30.90	8.00	30.50	FPC-0.5FZ-59PLBR-H54	59	29.00	30.06	33.00	31.40	8.00	31.00	FPC-0.5FZ-60PLBR-H54	60	29.50	30.56	33.50	31.90	8.00	31.50
P/N	PIN	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F																																																																																																																																																											
FPC-0.5FZ-5PLBR-H54	5	2.00	3.06	6.00	4.40	2.50	4.00																																																																																																																																																											
FPC-0.5FZ-6PLBR-H54	6	2.50	3.56	6.50	4.90	3.00	4.50																																																																																																																																																											
FPC-0.5FZ-7PLBR-H54	7	3.00	4.06	7.00	5.40	3.00	5.00																																																																																																																																																											
FPC-0.5FZ-8PLBR-H54	8	3.50	4.56	7.50	5.90	4.00	5.50																																																																																																																																																											
FPC-0.5FZ-9PLBR-H54	9	4.00	5.06	8.00	6.40	4.00	6.00																																																																																																																																																											
FPC-0.5FZ-10PLBR-H54	10	4.50	5.56	8.50	6.90	4.00	6.50																																																																																																																																																											
FPC-0.5FZ-11PLBR-H54	11	5.00	6.06	9.00	7.40	4.00	7.00																																																																																																																																																											
FPC-0.5FZ-12PLBR-H54	12	5.50	6.56	9.50	7.90	4.00	7.50																																																																																																																																																											
FPC-0.5FZ-13PLBR-H54	13	6.00	7.06	10.00	8.40	4.00	8.00																																																																																																																																																											
FPC-0.5FZ-14PLBR-H54	14	6.50	7.56	10.50	8.90	4.00	8.50																																																																																																																																																											
FPC-0.5FZ-15PLBR-H54	15	7.00	8.06	11.00	9.40	4.00	9.00																																																																																																																																																											
FPC-0.5FZ-16PLBR-H54	16	7.50	8.56	11.50	9.90	4.00	9.50																																																																																																																																																											
.....																																																																																																																																																																		
FPC-0.5FZ-56PLBR-H54	56	27.50	28.56	31.50	29.90	8.00	29.50																																																																																																																																																											
FPC-0.5FZ-57PLBR-H54	57	28.00	29.06	32.00	30.40	8.00	30.00																																																																																																																																																											
FPC-0.5FZ-58PLBR-H54	58	28.50	29.56	32.50	30.90	8.00	30.50																																																																																																																																																											
FPC-0.5FZ-59PLBR-H54	59	29.00	30.06	33.00	31.40	8.00	31.00																																																																																																																																																											
FPC-0.5FZ-60PLBR-H54	60	29.50	30.56	33.50	31.90	8.00	31.50																																																																																																																																																											
4																																																																																																																																																																		
			<table><thead><tr><th colspan="2">GENERAL TOLERANCE</th><th colspan="2">DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD</th><th colspan="2">BXCONN®</th></tr></thead><tbody><tr><td colspan="2">DIM. TOL. .x ±0.50 .xx ±0.20 .xxx ±0.10 GENERAL ANGLE: ±1°</td><td colspan="2">TITLE: 0.5 Pitch微盖立式正脚(H=5.4)</td><td colspan="2">QR CODE</td></tr><tr><td colspan="2">DWG. NO.: FC-05FXP21H54</td><td colspan="2">CHECKED: MAX</td><td colspan="2" rowspan="2">APPROVED: WILL</td></tr><tr><td colspan="2">PART NO.: FC-05FXP21H54</td><td colspan="2">DRAWN: ELLA</td></tr><tr><td>UNIT: mm</td><td>SCALE: none</td><td>SHEET: 1 of 1</td><td>DWG. SIZE: A4</td><td>LAYER: bxconn</td><td></td></tr></tbody></table>								GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD		BXCONN®		DIM. TOL. .x ±0.50 .xx ±0.20 .xxx ±0.10 GENERAL ANGLE: ±1°		TITLE: 0.5 Pitch微盖立式正脚(H=5.4)		QR CODE		DWG. NO.: FC-05FXP21H54		CHECKED: MAX		APPROVED: WILL		PART NO.: FC-05FXP21H54		DRAWN: ELLA		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn																																																																																																																													
GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD		BXCONN®																																																																																																																																																														
DIM. TOL. .x ±0.50 .xx ±0.20 .xxx ±0.10 GENERAL ANGLE: ±1°		TITLE: 0.5 Pitch微盖立式正脚(H=5.4)		QR CODE																																																																																																																																																														
DWG. NO.: FC-05FXP21H54		CHECKED: MAX		APPROVED: WILL																																																																																																																																																														
PART NO.: FC-05FXP21H54		DRAWN: ELLA																																																																																																																																																																
UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn																																																																																																																																																														