







标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

PIN 数	A±0.1	B±0.1	C±0.1
2P	7.60	4.50	1.25
3P	8.85	5.75	2.50
4P	10.10	7.00	3.75
5P	11.35	8.25	5.00
6P	12.60	9.50	6.25
7P	13.85	10.75	7.50
8P	15.10	12.00	8.75
9P	16.35	13.25	10.00
10P	17.60	14.50	11.25
11P	18.85	15.75	12.50
12P	20.10	17.00	13.75



Specifications:

Rated Voltage : 125V AC/DC

Rated Current : 1A AC,DC

Withstand Voltage : 200V AC/minute

Contact Resistance : 50mΩ(MAX.)

Insulation Resistance : 100MΩ(MIN.)

Storage Temperature Range: -40°C~+85°C;

Operation Temperature Range: -25°C~+70°C;

2	插针	铜	镀镍锡	
1	基座	LCP	米色	
序号	品名	材 质	电镀/颜色	备注



深圳市虹成电子有限公司

品 名 TITLE	针座
料 号 PART NO	HCZZ0015-11

UNLESS OTHERWISE,
GENERAL TOLERANCE:X. xxx ±0.05
X. xx ±0.15
X. x ±0.25

ANGULAR:

X. xx° ±1°
X. x° ±3°
X. ° ±5°比 例
SCALE

1:1

单 位
UNIT

MM

张 数
PART NO

1 OF 1

版 本
REV

A

制 图
DRAW

AhYe

审 核
CHECKED

夏操云

批 准
APPROVE

赵亮亮

