



标记
MARKECN编号/变更内容
ECN NO/DEFINITION修改
REVISE日期
DATE核准
APPROVE

Pin	DIM A	DIM B	DIM C
2	4.50	1.50	3.60
3	6.00	3.00	5.10
4	7.50	4.50	6.60
5	9.00	6.00	8.10
6	10.50	7.50	9.60
7	12.00	9.00	11.10
8	13.50	10.50	12.60
9	15.00	12.00	14.10
10	16.50	13.50	15.60
11	18.00	15.00	17.10
12	19.50	16.50	18.60
13	21.00	18.00	20.10
14	22.50	19.50	21.60
15	24.00	21.00	23.10
16	25.50	22.50	24.60



技术要求:

适应基板厚度: 1.2mm~1.6mm



温度范围: -25℃~85℃

额定电压: 100V AC/DC

额定电流: 1A

绝缘电阻: ≥1000MΩ

耐压: 800V AC/minute



2	插针	铜	镀锡	
1	底座	PA66	米色	
序号	品名	材质	电镀/颜色	备注



深圳市虹成电子有限公司

品名 TITLE	针座
料号 PART NO	HCZZ0002-3

GENERAL TOLERANCES
(UNLESS SPECIFIED)比例
SCALE

1:1



XX ±0.35

X' ±3.00"

单位
UNIT

MM

制图
DRAW

AhYe

XX ±0.25

X' ±2.00"

张数
PART NO

1 OF 1

审核
CHECKED

夏操云

XXX ±0.15

X' ±1.00"

版本
REV

A

批准
APPROVE

赵亮亮

