



RoHS
Compliant

结构图面

REV	DESCRIPTION	APPR	CHECK	DRAW	DATE
A	原始图档		JACK	Yang	160606



RECOMMENDED P.C.BOARD LAYOUT






说明:

- 主体: PA9T(UL94V-0)/LCP 颜色: 黑
- 端子: 磷铜镀金 T=0.20mm

电气性能:

- 额定电压: 30V(Max) AC/DC;
- 绝缘耐压: AC 1KV 1分钟, 相邻端子间无损坏
- 绝缘阻抗: 1000M Ω , 500V DC 1分钟相邻端子间
- 使用温度: -25℃~+80℃



Table

PART NUMBER	P / N	Dim A	Dim B	Dim C
JME2F03-H250001CT-B	03pin	8.00	4.00	7.35
JME2F04-H250001CT-B	04pin	10.00	6.00	9.35
JME2F05-H250001CT-B	05pin	12.00	8.00	11.35
JME2F06-H250001CT-B	06pin	14.00	10.00	13.35
JME2F07-H250001CT-B	07pin	16.00	12.00	15.35
JME2F08-H250001CT-B	08pin	18.00	14.00	17.35

QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		SCALE:	SOURCE:	TITLE:
			1:1	100%	
 	MM	INCH	REWORK:	DATE:	东莞市文章济美电子有限公司 Battery 2.0PH 90度 插贴式母座
	-I ±0.25	-I	DATE:	DATE:	
	-XX ±0.15	-XX	DATE:	DATE:	
	-XXX ±0.05	-XXX	DATE:	DATE:	
ANGULAR ±1°			DATE:	DATE:	 DATE: JME3FX-H250001CT-B DATE: 1/1
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			DATE:	DATE:	