



标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

Pin	DIM A	DIM B	DIM C	DIM D
2	6.00	2.00	4.90	0.80
3	8.00	4.00	6.90	2.80
4	10.00	6.00	8.90	4.80
5	12.00	8.00	10.90	6.80
6	14.00	10.00	12.90	8.80
7	16.00	12.00	14.90	10.80
8	18.00	14.00	16.90	12.80
9	20.00	16.00	18.90	14.80
10	22.00	18.00	20.90	16.80
11	24.00	20.00	22.90	18.80
12	26.00	22.00	24.90	20.80
13	28.00	24.00	26.90	22.80
14	30.00	26.00	28.90	24.80
15	32.00	28.00	30.90	26.80
16	34.00	30.00	32.90	28.80



技术要求:

适应基板厚度: 1.2mm~1.6mm



温度范围: -25°C~85°C

额定电压: 200V AC/DC

额定电流: 1A

绝缘电阻: ≥1000MΩ

耐 压: 800V AC/minute



2	插针	铜	镀锡	
1	基座	PA66	米色	
序号	品名	材 质	电镀/颜色	备注



深圳市虹成电子有限公司

品 名 TITLE	针座
料 号 PART NO	HCZZ0256-13

GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1	制 图 DRAW		AhYe	
X.X ±0.35	X' ±3.00"	单 位 UNIT	MM	张 数 PART NO	1 OF 1	审 核 CHECKED	
X.XX ±0.25	X.X' ±2.00"	版 本 REV	A	制 图 DRAW	夏操云	批 准 APPROVE	
X.XXX ±0.15	X.XX' ±1.00"					赵亮亮	