



Pin	DIM A	DIM B	DIM C
2	4.50	1.50	3.60
3	6.00	3.00	5.10
4	7.50	4.50	6.60
5	9.00	6.00	8.10
6	10.50	7.50	9.60
7	12.00	9.00	11.10
8	13.50	10.50	12.60
9	15.00	12.00	14.10
10	16.50	13.50	15.60
11	18.00	15.00	17.10
12	19.50	16.50	18.60
13	21.00	18.00	20.10
14	22.50	19.50	21.60
15	24.00	21.00	23.10
16	25.50	22.50	24.60



耐 压: 800V AC/minute

	深圳市虹成电子有限公司		品 名	针座	
			TITLE		
			料 号	HCZZ0445-9	
GENERAL TOLERANCES (UNLESS SPECIFIED)			比 列 SCALE	1 : 1	
X.X ±0.35	X* ±3.00"	单 位 UNIT	MM	制 图 DRAW	AhYe
X.XX ±0.25	X.X* ±2.00"	张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云
X.XXX ±0.15	X.XX* ±1.00"	版 本 REV	A	批 准 APPROVE	赵亮亮
					