




REV.	Q'TY	ECN. NO.	APR.	DATE




RECOMMENDED PCB LAYOUT  
GENERAL TOLERANCE ±0.05



SPECIFICATIONS

- CURRENT RATING: 0.3A .
- VOLTAGE RATING 30V AC/DC.
- TEMPERATURE RANGE:-35°C TO +85°C
- CONTACT RESISTANCE: 90mΩ MAX.
- INSULATION RESISTANCE: 50 MΩ MIN.
- WITHSTANDING VOLTAGE: 100V AC/MINUTE.



PIN	A	B	HC
XY-10DS-DF40HC	4.6	1.6	1.0
XY-12DS-DF40HC	5.0	2.0	
XY-20DS-DF40HC	6.6	3.6	
XY-24DS-DF40HC	7.4	4.4	1.2
XY-30DS-DF40HC	8.6	5.6	1.5
XY-34DS-DF40HC	9.4	6.4	2.3
XY-40DS-DF40HC	10.6	7.6	3.2
XY-50DS-DF40HC	12.6	9.6	
XY-60DS-DF40HC	14.6	11.6	
XY-70DS-DF40HC	16.6	13.6	
XY-80DS-DF40HC	18.6	15.6	
XY-90DS-DF40HC	20.6	17.6	
XY-100DS-DF40HC	22.6	19.6	

The product is high	H
XY-XDS-DF40HC	1.45
XY-XDS-DF420HC	1.95
XY-XDS-DF240HC	2.40
XY-XDS-DF429HC	2.90
XY-XDS-DF434HC	3.40
XY-XDS-DF439HC	3.90

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		TITLE: 0.40MM BTB SOCKET			
.X±0.5	X.*± 2	APR. Alex	DWG NO. XY-NDS-DF40HC		
.XX±0.35	.X*± 1	CHK. Jack	PROJ.  CUSTOMER DRAWING		
.XXX±0.25	.XX*±	DRA. Can	SIZE A4	SCALE 1:1	SHEET 1/1
				REV. A	