






标 记  
MARKECN编号/变更内容  
ECN NO/DEFINITION修 改  
REVISE日 期  
DATE核 准  
APPROVE

| PIN 数 | A±0.15 | B±0.15 | C±0.15 |
|-------|--------|--------|--------|
| 13P   | 21.35  | 18.25  | 15.00  |
| 14P   | 22.60  | 19.50  | 16.25  |
| 15P   | 23.85  | 20.75  | 17.50  |
| 16P   | 25.10  | 22.00  | 18.75  |





3D View



## Specifications:

- 1.Rated Voltage : 125V AC/DC
- 2.Rated Current : 1A AC,DC
- 3.Withstand Voltage : 200V AC/minute
- 4.Contact Resistance : 50mΩ(MAX.)
- 5.Insulation Resistance : 100MΩ(MIN.)
- 6.Storage Temperature Range: -40°C~+85°C;
- 7.Operation Temperature Range: -25°C~+70°C;



| 2   | 插针  | 铜   | 镀镍锡   |     |
|-----|-----|-----|-------|-----|
| 1   | 基座  | LCP | 米色    |     |
| 序 号 | 品 名 | 材 质 | 电镀/颜色 | 备 注 |



深圳市虹成电子有限公司

| 品 名<br>TITLE   | 针座          |
|----------------|-------------|
| 料 号<br>PART NO | HCZZ0001-15 |

UNLESS OTHERWISE,  
GENERAL TOLERANCE:X. xxx ±0.05  
X. xx ±0.15  
X. x ±0.25

ANGULAR:

X. xx° ±1°  
X. x° ±3°  
X. ° ±5°比 例  
SCALE

1:1

单 位  
UNIT

MM

张 数  
PART NO

1 OF 1

版 本  
REV

A

制 图  
DRAW

AhYe

审 核  
CHECKED

夏操云

批 准  
APPROVE

赵亮亮

