

概述 Summary

- 单组输出：功率35W
Single output: power 35W
- 输入电压:90~240VAC/127~370VDC
Input voltage:90~240VAC/127~370VDC

99x82x 30mm



常见规格 General Specification

性能 Specification	型号 Model	SDU-E35-12	SDU-E35-15	SDU-E35-24	SDU-E35-48
直流输出电压、电流 DC output voltage, current		12V 0~3A	15V 0~2.4A	24V 0~1.5A	48V 0~0.8A
纹波及噪音 Wave and noise		120mVp-p	120mVp-p	150mVp-p	200mVp-p
进线稳定度 Inlet wire stability		± 0.5%	± 0.5%	± 0.5%	± 0.5%
负载稳定度 Load stability		± 0.5%	± 0.5%	± 0.5%	± 0.5%
效率 Efficiency		86%	88%	88%	90%
直流电压可调范围 Adjustable range for DC voltage		± 10%	± 10%	± 10%	± 10%
输入电压范围 Input voltage range		90~240V交流 1127~370V直流 47~63Hz 90~240VAC 1127~370VDC 47~63Hz			
冲击电流 Impact current		冷启动电流 45A/230VAC Cold start current			
过载保护 Overload protection		110% ~ 150%切断输出，自动恢复 110% ~ 150% cut off the output, automatic recovery			
其他保护 Other protection		过流保护/短路保护 Overcurrent protection / Short-circuit protection			
启动、上升、保持时间 Setup, rise, hold up time		1000ms, 30ms/230VAC 2000ms, 30ms/115VAC			
耐压性 Withstand voltage		输入输出间: 1.5kV 输入与外壳间: 1.5kV 输出与外壳间: 0.5kV 一分钟 I/P-O/P: 1.5kV I/P-FG: 1.5kV O/P-FG: 0.5kV 1minute			
隔离电阻 Isolation resistance		输入输出间 输入与外壳间 输出与外壳间: 500VDC/100M I/P-O/P I/P-FG O/P-FG: 100M Ohms / 500VDC / 25℃ / 70%RH			
工作温度 Working temperature		-20℃ ~ +70℃			
尺寸 Dimension		99x 82 x 30mm			
重量 Weight		0.23kg			
包装 Packing		44x36.5x19.5CM/80PCS/16kg			

外形尺寸 Overall dimension(mm)

- ☑ 接线位置
- ☑ 端口 1,2: 交流输入
 - ☑ 端口 3: 接地
 - ☑ 端口 4: 直流输出-V
 - ☑ 端口 5: 直流输出+V
- ☑ Terminal Pin No. Assignment
- ☑ Pin 1,2 : AC input
 - ☑ Pin 3 : GND
 - ☑ Pin 4 : DC output-V
 - ☑ Pin 5 : DC output+V

