







标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE



No. of Contacts	DIM A	DIM B	DIM C
2	2.5	10.0	6.20
3	5.0	12.5	8.70
4	7.5	15.0	11.20
5	10.0	17.5	13.70
6	12.5	20.0	16.20





2*8 (含8Y) 以下

SPECIFICATIONS

- 1.Current Rating: 3A AC, DC
- 2.Voltage Rating: 250V AC, DC
- 3.Temperatuer Range: -25°C~+85°C
- 4.Contact Resistance: 20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 1000V AC/minute
- 7.Material: PA66



2*4Y



2*5Y-2*8Y

1	胶壳	PA66	白色	
序号	品名	材质	电镀/颜色	备注




深圳市虹成电子有限公司

品名 TITLE	胶壳
料号 PART NO	HC-XAD2. 54-2x4Y

GENERAL TOLERANCES
(UNLESS SPECIFIED)比 列
SCALE

1:1



X.±0.25	X.*±2°
.X±0.25	.X*±1°
.XX±0.15	.XX*±0.5°
.XXX±0.10	.XXX*±0.5°

单位 UNIT	MM
张数 PART NO	1 OF 1
版本 REV	A

制图 DRAW	AhYe
审核 CHECKED	夏操云
批准 APPROVE	赵亮亮

