






REV.	DESCRIPTION	APPD	DATE
△	移动焊脚位由9.95改为10.15	PENTIUM	0403'10




NOTES:

- 1.MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC
UL94V_0,COLOR:BLACK.
CONTACT: COPPER ALLOYS.
COVER: COPPER ALLOYS OR STEEL.
- 2.PLATING:
UNDERPLATE: NICKEL.
CONTACT AREA: GOLD OVER NICKEL.
SOLDER AREA: TIN OVER NICKEL.
- 3.MULTIMEDIA CARD COMPATIBLE

定订须知: TFS10-00XX-X000-A



RECOMMENDED P.C.B HOLE
LAYOUT
COMPONENT SIDE VIEW(TOLERANCE:
+/-0.05)



PIN NO.	NAME
1	DAT2
2	CD/DAT3
3	CMD
4	VDD
5	CLX
6	VSS
7	DATO
8	DAT1

PART NO:	TFS10-00XX-X000-A	MATERIAL:	
LOT NO:		FINSH:	
UNIT:	MM	COLOR:	
SIZE:	A4	DR:	陈凯 082709
GENERAL ANGLE:		CHK:	
X.X=±0.35		X.XX=±5.0'	
X.XX=±0.25		X.XXX=±3.0'	
X.XXX=±0.15		APP:	
TITLE:		T-FLASH简易全塑卡座	
DWF:		TFS10-XXXX-2000-A	
SCALE:		1:1	
SHEET:		1 OF 3	
REV:		A	

东莞市高铨达电子科技有限公司