





Circuit Diagram



Main Specifications:

主要技术指标:

Climate grade: -30℃ ~ +80℃

气候等级: -30℃ ~ +80

Rated values: Max50 Ma12V, DC Min10 uA1V DC

额定值: Max50 Ma12V, DC Min10 uA1V DC

Contact resistance: ≤100m Ω

接触电阻: ≤100m Ω

Dielectric strength: 250V AC 1Min

耐压: 250V AC 1Min

Insulation resistance: ≥100MΩ

绝缘电阻: ≥100MΩ

Travel: 0.20±0.10mm

行程: 0.20±0.10mm

Life: 200000

寿命: 200000

TP1033 □ □ □ □

Height

15 : 1.5mm

20 : 2.0mm

Actuation Force

16 : 160gf

26 : 260gf

6	Upper cover 上盖	1	SUS 不锈钢	
5	Push Button 按钮	1	LCP	Black 黑色
4	Terminal 端子	1	Phosphor bronze 磷青铜	Silver plating 镀银
3	Yellow Membrane 黄膜	1	PI	Yellow 黄色
2	Shrapnel 弹片	1	SUS 不锈钢	Silver plating 镀银
1	Plastic base 塑胶底座	1	LCP	Black 黑色
NO	Name	PCS	Materials	Notes

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX ± 0.10

X.X ± 0.15

X ± 0.25

ANGULAR

UNIT

MM

PROJECTED



PRODUCT NAME: TP1033 □ □ □ □

DRAWN BY

SHUHAO

CHECKED BY

COCO

MODEL NO:

DATE

2019

APPROVAL B

ALEN

Https: www.rocpcu.tw

ROCPCU TECHNOLOGY CO., LTD

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission