








| | | | |
|-----|-------------|-------------|------------|
| REV | ECN No. | DESCRIPTION | DATE |
| A | EC-22111101 | RELEASE | 2022.11.11 |



| PIN | A | B | C |
|-----|-------|-------|-------|
| 02 | 1.25 | 7.25 | 3.05 |
| 03 | 2.50 | 8.50 | 4.30 |
| 04 | 3.75 | 9.75 | 5.55 |
| 05 | 5.00 | 11.00 | 6.80 |
| 06 | 6.25 | 12.25 | 8.05 |
| 07 | 7.50 | 13.50 | 9.30 |
| 08 | 8.75 | 14.75 | 10.55 |
| 09 | 10.00 | 16.00 | 11.80 |
| 10 | 11.25 | 17.25 | 13.05 |
| 11 | 12.50 | 18.50 | 14.30 |
| 12 | 13.75 | 19.75 | 15.55 |
| 13 | 15.00 | 21.00 | 16.80 |
| 14 | 16.25 | 22.25 | 18.05 |
| 15 | 17.50 | 23.50 | 19.30 |
| 16 | 18.75 | 24.75 | 20.55 |



RECOMMEND PCB LAYOUT
TOLERANCE:±0.05

| 序号 | 名称 | 数量 |
|----|-------|----|
| 1 | 基座 | 1 |
| 2 | 阳接触针 | n |
| 3 | 焊片 | 2 |
| 4 | COVER | 1 |

说明:

1. 产品表面清洁, 无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
2. 塑胶材料: H-TEMP PLASTIC 颜色: 本色;
3. 金属材料: 黄铜, 镀锡;

| | | | | | |
|----------------------------------|--|------------|--|---------------------------------------|------------------|
| 东莞市高钺达电子科技有限公司 惠州市高钺达光电科技有限公司 | | | NAME(INTENDED USE) CUSTOMER DRAWING | | |
| APPROVALS | | DATE | | TOLERANCES UNLESS OTHERWISE SPECIFIED | PART NO.: |
| DR: | | 2022.11.11 | | X.±0.30 | X.±5° |
| CHKD: / | | | | .X±0.25 | .X±3° |
| APPD: | | 2022.11.11 | | .XX±0.20 | .XX±1° |
| | | | | | DESCRIPTION: |
| | | | | | WAF1.25立贴系列 |
| | | | | | WAFX-T1T1-2020-A |
| | | SIZE | UNITS | SCALE | SHEET |
| | | A4 | mm | 1:1 | 1/1 |