






REV	ECN No.	DESCRIPTION	DATE
A	EC-201119902	标准化	2020.11.19



PCB LAYOUT  
TOL.: ±0.05

No. of Contacts	Dimension		
	A	B	C
2	2.5	9.9	5.9
3	5.0	12.4	8.4
4	7.5	14.9	10.9
5	10.0	17.4	13.4
6	12.5	19.9	15.9
7	15.0	22.4	18.4
8	17.5	24.9	20.9
9	20.0	27.4	23.4
10	22.5	29.9	25.9
11	25.0	32.4	28.4
12	27.5	34.9	30.9
13	30.0	37.4	33.4
14	32.5	39.9	35.9
15	35.0	42.4	38.4
16	37.5	44.9	40.9



- NOTES:
- 1.MATERIAL:  
HOUSING:LCP NATURE  
TERMINAL:BRASS  
PEG:PHOSPHOR BRONZE
  - 2.PLATING:  
TIN OVER NICKEL
  - 3.RATING:  
CURRENT RATING:3A DC//AC  
VOLTAGE RATING:250V DC//AC  
TEMPERATURE RANGE:-40~+85°C

东莞市高敏达电子科技有限公司

APPROVALS	DATE	TOLERANCES UNLESS OTHERWISE SPECIFIED	PART NO.:	NAME:(INTENDED USE)
Z.S	2020.10.08	X.±0.30	2.54间距贴片系列	客户图
CHKD: /		X.±0.25	DRAWING NO.:	
APPD: Z.X.LI	2020.10.08	.XX±0.20	/ 8800-XXA4-TG	
			SIZE	UNITS
			A4	mm
			SCALE	SHEET
			1:1	1/1