


2P

3P~4P

Ordering Information:

A2012H-XP - *** - ***
1 2 3

1.Part NO.

2.Material:

(Blank):Nylon 66,UL94V-0(White)

GWT: Nylon 66,UL94V-0(Beige),
IEC 60335-1,5th Edition
Glow Wire Capable.

3.Color:


(Blank): see section 2 material

BK: Black

RD: Red

BL: Blue

YL: Yellow



SPECIFICATIONS:

Current Rating: 3A AC,DC

Voltage Rating: 250V AC,DC

Temperature Range: -40°C ~ +105°C



Contact Resistance: 10mΩ Max.

Insulation Resistance: 1000MΩ Min.

Withstanding Voltage: 800V AC/minute

Ordering Information & Dimensions

Circuits	Dimensions(mm)			Circuits	Dimensions(mm)		
	A	B	C		A	B	C
2P	2.00	4.30	6.00	10P	18.00	20.30	22.00
3P	4.00	6.30	8.00	11P	20.00	22.30	24.00
4P	6.00	8.30	10.00	12P	22.00	24.30	26.00
5P	8.00	10.30	12.00	13P	24.00	26.30	28.00
6P	10.00	12.30	14.00	14P	26.00	28.30	30.00
7P	12.00	14.30	16.00	15P	28.00	30.30	32.00
8P	14.00	16.30	18.00	16P	30.00	32.30	34.00
9P	16.00	18.30	20.00				



5P~16P

CJTconn CHANGJIANG CONNECTORS CO.,LTD.

			Unit	Scale	Sheet	TITLE			
			mm	4:1	1 of 1				
A4	JL-GC-ECN00228	2024.01.19	DRAWN	CHK'D	APPR'D	2.00mm Pitch			
A3	CHANGE THE DRAWING	2023.07.07	Haisen Li	Diankui Wan	Jack Yin				
A2	UPDATED DRAWINGS	2022.09.27	General Tolerances		THIRD ANGLE PROJECTION	Housing			
A1	CHANGE THE DIMENSIONS	2019.06.27	x.xx±0.25 x.xxx±0.20 x.xxxx±0.15 ANGLES ±1°						
A0	NEW RELEASE	2012.12.27				DRAWING NO. A2012H-XP			
REV	DESCRIPTION	DATE							