







RoHS



PCB Layout(Pattern side)



Circuit Diagram



Product No. : TS-061D-□□□

型号:

: 包装方式
-P=编带(非编带, 不启用)

操作力度:
180=180gf±50gf
250=250gf±50gf

: 弹片
D2=SUS/1PCS
D4=SUS/2PCS

Ⓕ	Dust film		1	Polyimide tape	
Ⓖ	Terminal		3	Phosphorus bronze	Silvering
Ⓓ	Reed		2	SUS	Silvering
Ⓒ	Base		1	LCP	Black
Ⓑ	Cover		1	Phosphorus bronze	Silvering
Ⓐ	Button		1	LCP	Black
NO.	Name	Number	Qty	Materil	Remarks

ZHONGDI® Zhongdi Electronic Technology Co., Ltd

design	date	name	TACT SWITCHS
Review	date	model	TS-061D-□D□
Approved	date		

Drawing number: A4

modify Review Approved

angle ±2°
10~30 ±0.30
5~10 ±0.20
~ 5 ±0.10

Tolerance not specified

Proportion 1:1 unit mm gage number


项 目 Item	技术参数 Technical Parameter	标 准 Standard
电气性能 Electrical Properties	额定电流 Rated Current:	50mA
	额定电压 Rated voltage:	DC 12V
	接触电阻 Contact resistance:	≤100mΩ
	绝缘电阻 Insulation Resistance:	DC 250V 1 min ≥100MΩ
	耐压强度 Compressive strength:	AC 250V 50Hz/1 min
机械 性能 Mechanical Properties	机械寿命 Mechanical life:	100,000 cycles Min
	操作行程 Operation Stroke:	0.20mm±0.10mm
环境性能 Environmental	工作温度 Operation temperature:	-25℃～ +75℃
	使用湿度 Use humidity:	≤85% RH
可靠性特性 Reliability Characteristics	回流焊 Reflow Soldering:	≤260℃ 时间 Time 3s
	波峰焊 Wave soldering:	
	手工焊 Manual welding:	≥260℃ 时间 Time 3s
应用领域 Application area	影音产品、电子玩具、数码产品、通讯产品、安防产品等. Audiovisual products, electronic toys, digital products, communication products, security products, etc	



绝缘电阻测量仪



直流低电阻测试仪




耐电压测试仪



回流焊机



二次元測量儀



精密寿命测试仪



盐雾测试仪



按键荷重曲线仪

 Zhongdi Electronic Technology Co., Ltd.									
design		date		name		TACT SWITCHS			
Review		date		model		TS-061D-□D□			
Approved		date							
number:									
pn	1:1	unit	mm	cape number				A4	