






SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -40°C~ +105°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Housing LCP UL94V-0
PIN Brass Tin-plated



Circuit	Part NO.	Dimensions mm			
		A	B	C	D
2	HC-HY-2A-LCP-05	2.00	6.00	4.90	2.90
3	HC-HY-3A-LCP-05	4.00	8.00	6.90	3.30
4	HC-HY-4A-LCP-05	6.00	10.00	8.90	3.50
5	HC-HY-5A-LCP-05	8.00	12.00	10.90	5.50
6	HC-HY-6A-LCP-05	10.00	14.00	12.90	7.50
7	HC-HY-7A-LCP-05	12.00	16.00	14.90	9.50
8	HC-HY-8A-LCP-05	14.00	18.00	16.90	11.50
9	HC-HY-9A-LCP-05	16.00	20.00	18.90	13.50
10	HC-HY-10A-LCP-05	18.00	22.00	20.90	15.50
11	HC-HY-11A-LCP-05	20.00	24.00	22.90	17.50
12	HC-HY-12A-LCP-05	22.00	26.00	24.90	19.50
13	HC-HY-13A-LCP-05	24.00	28.00	26.90	21.50
14	HC-HY-14A-LCP-05	26.00	30.00	28.90	23.50
15	HC-HY-15A-LCP-05	28.00	32.00	30.90	25.50
16	HC-HY-16A-LCP-05	30.00	34.00	32.90	27.50
17	HC-HY-17A-LCP-05	32.00	36.00	34.90	29.50
18	HC-HY-18A-LCP-05	34.00	38.00	36.90	31.50
19	HC-HY-19A-LCP-05	36.00	40.00	38.90	33.50
20	HC-HY-20A-LCP-05	38.00	42.00	40.90	35.50



			GENERAL TOLERANCE	制图	深圳市华灿天禄电子有限公司			
			DIM TOL	审核	ShenzhenhuacantianluELECTRONICS CO., LTD			
			X.X ±0.30	批准	产品名称	HY (2.0)单排带扣直针	版本	A
			X.XX ±0.20	比例	产品料号	HC-HY-NA-LCP-05	单位	mm
			X.XXX ±0.10	投影	材料		页次	1/1
1	初版发行	日期	Angle ±3.0°	Projection			SHEET	
序号	变更内容	日期						
No.	MODIFY CONTENT	MODIFY DATE						