


Feature:

- ◆ Complying with IEEE 802.3ab standard for 1000 BASE-T.
- ◆ Comply with RoHS & Halogen Free requirements.
- ◆ Supports 4 pairs of category 5 UTP cable.
- ◆ Operating Temperature: - 40°C~+85°C.
- ◆ Storage temperature range: -20°C to + 85°C.


Electrical Specification @25°C

Inductance:	350uH Min. @100KHz/0.1V 8mA DC Bias		
Hi-POT :	1500VAC/1Sec/1mA		
Leakage inductance:	0.5uH Max. @100KHz/0.1V		
C.W.W.	30pF Max. @100KHz/0.1V		
D.C.R:	1.2 Ω max		
Turn Ratio:	1CT:1CT $\pm$ 2%		
Insertion Loss:	-1.2dB Max.@1-100MHz:		
Return Loss:	1-30MHz	30-60 MHz	60-100MHz
	-16dB Min.	-14.4dB Min.	-10dB Min.
D.C.M.R :	-40dBMin.@30MHz	-35dBMin@60MHz	-30dBMin.@100MHz
Cross Talk :	-45dBMin.@1-30MHz	-40dBMin.@30-60MHz	-35dBMin.@60-100MHz

Schematic:



Mechanical:



Packing:300PCS/Reel