


SPECIFICATIONS

1. Current Rating: 2A AC, DC
2. Voltage Rating: 250V AC, DC
3. Temperature Range: -25°C ~ +85°C
4. Contact Resistance: 20mΩ Max
5. Insulation Resistance: 1000mΩ Min
6. Withstanding Voltage: 800V AC/minute
7. Material: Wafer LCP UL94V-0
PIN Brass Tin-plated

Circuit	Part NO.	Dimensions mm		
		A	B	C
2	HC-PHB-2x2A-LCP-05	2.00	6.00	4.90
3	HC-PHB-2x3A-LCP-05	4.00	8.00	6.90
4	HC-PHB-2x4A-LCP-05	6.00	10.00	8.90
5	HC-PHB-2x5A-LCP-05	8.00	12.00	10.90
6	HC-PHB-2x6A-LCP-05	10.00	14.00	12.90
7	HC-PHB-2x7A-LCP-05	12.00	16.00	14.90
8	HC-PHB-2x8A-LCP-05	14.00	18.00	16.90
9	HC-PHB-2x9A-LCP-05	16.00	20.00	18.90
10	HC-PHB-2x10A-LCP-05	18.00	22.00	20.90
11	HC-PHB-2x11A-LCP-05	20.00	24.00	22.90
12	HC-PHB-2x12A-LCP-05	22.00	26.00	24.90
13	HC-PHB-2x13A-LCP-05	24.00	28.00	26.90
14	HC-PHB-2x14A-LCP-05	26.00	30.00	28.90
15	HC-PHB-2x15A-LCP-05	28.00	32.00	30.90
16	HC-PHB-2x16A-LCP-05	30.00	34.00	32.90
17	HC-PHB-2x17A-LCP-05	32.00	36.00	34.90
18	HC-PHB-2x18A-LCP-05	34.00	38.00	36.90
19	HC-PHB-2x19A-LCP-05	36.00	40.00	38.90
20	HC-PHB-2x20A-LCP-05	38.00	42.00	40.90
21	HC-PHB-2x21A-LCP-05	40.00	44.00	42.90
22	HC-PHB-2x22A-LCP-05	42.00	46.00	44.90
23	HC-PHB-2x23A-LCP-05	44.00	48.00	46.90
24	HC-PHB-2x24A-LCP-05	46.00	50.00	48.90
25	HC-PHB-2x25A-LCP-05	48.00	52.00	50.90

Ordering Information



			GENERAL TOLERANCE	制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM TOL	审核 CHECK	产品名称 TITLE	PHB (2.0) 双排 直针	版本 REV.	A
			X.X ±0.30	批准 APPROVAL	产品料号 PART NO.	HC-PHB-2xNA-LCP-05	单位 UNITS	mm
			X.XX ±0.20	比例 SCALE	材料 MATERIAL		页次 SHEET	1/1
			X.XXX ±0.10	投影 Projection				
			Angle ±3.0°					
1	初版发行							
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						