




A		B		C		D		E																																				
序号	线材名称	材料规格(符合ROHS)	用量	单位	备注	REV.	DESCRIPTION	ECN NO.	NAME	DATE																																		
1	1	胶壳	WF-1D254B3P	1	pcs	技术要求: 1.1 端子铆接牢固,无松动,脱落现象; 1.2 线材印字清晰,无破损划伤; 1.3 端子与线材拉力值:≥2.5kg; 1.4 线材两端100%导通,无短/断路 1.5 外观要求按品质管理部检验标准执行 1.6 包装要求按包装作业指引或者客户制定包装要求																																						
	2	端子	WF-1C254B	3	pcs						按照图中线序方向打端和插壳,端子与胶壳连																																	
2	3	线材	UL1007 24# OD1.4mm 11*0.16TS 红色	200	mm						裁线长度:见材料表,裁线公差±2mm;																																	
	4	线材	UL1007 24# OD1.4mm 11*0.16TS 黑色	200	mm						裁线长度:见材料表,裁线公差±2mm;																																	
	5	线材	UL1007 24# OD1.4mm 11*0.16TS 黄色	200	mm						裁线长度:见材料表,裁线公差±2mm;																																	
3(红) 4(黑) 5(黄) 1-2   可定制:线长、颜色、顺序、单双头、同/反向、裸铜长度... <table><tr><td colspan="2">GENERAL TOLERANCE</td><td colspan="3">DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD</td></tr><tr><td>DIM.</td><td>TOL.</td><td colspan="3">TITLE: Terminal wiring</td></tr><tr><td>0~100</td><td>±2mm</td><td>DWG. NO.:</td><td>XHB3P-24AWG-200-A1T</td><td>CHECKED: MAX</td></tr><tr><td>100~200</td><td>±3mm</td><td>PART NO.:</td><td>XHB3P-24AWG-200-A1T</td><td>DRAWN: ELLA</td></tr><tr><td>200~300</td><td>±5mm</td><td>UNIT: mm</td><td>SCALE: none</td><td>SHEET: 1 of 1</td></tr><tr><td>GENERAL ANGLE:</td><td></td><td>DWG. SIZE: A4</td><td>LAYER: bxconn</td><td>APPROVED: WILL</td></tr><tr><td>X°:</td><td>±5°</td><td colspan="3" rowspan="3">   </td></tr><tr><td>X.X°:</td><td>±3°</td></tr><tr><td>X.XX°:</td><td>±1°</td></tr></table> 						GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD			DIM.	TOL.	TITLE: Terminal wiring			0~100	±2mm	DWG. NO.:	XHB3P-24AWG-200-A1T	CHECKED: MAX	100~200	±3mm	PART NO.:	XHB3P-24AWG-200-A1T	DRAWN: ELLA	200~300	±5mm	UNIT: mm	SCALE: none	SHEET: 1 of 1	GENERAL ANGLE:		DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL	X°:	±5°	 			X.X°:	±3°	X.XX°:	±1°
GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD																																										
DIM.	TOL.	TITLE: Terminal wiring																																										
0~100	±2mm	DWG. NO.:	XHB3P-24AWG-200-A1T	CHECKED: MAX																																								
100~200	±3mm	PART NO.:	XHB3P-24AWG-200-A1T	DRAWN: ELLA																																								
200~300	±5mm	UNIT: mm	SCALE: none	SHEET: 1 of 1																																								
GENERAL ANGLE:		DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL																																								
X°:	±5°	 																																										
X.X°:	±3°																																											
X.XX°:	±1°																																											