








A

B

C


D

E




MATING PLUG Ø5.6xØ0.9mm

SCHMATIC



CIRCUIT DIAGRAM



RECOMMENDED PCB LAYOUT  
TOLERANCE:±0.05



SCALE: 1:1 UNIT: mm  
SIZE: A4

Title: Horizontal DC Power Jack 7909  
DIP CH=6.83 Ø1.0mm

Unless otherwise  
General tolerance:  
X ±0.50  
X.x ±0.30  
X.xx ±0.20  
X.xxx ±0.10  
X.x\* ±2\*

Molde Code: DC-S013A-D010-25A

DRAWN	CHECKED	APPROVED	DATE
Jiang	Xia	Chen	2023.05.21

品赞科技®  
**b-Switch**  
www.dg-switch.com

REV: A0 SHEET: 1/1

NO.	DESCRIPTION	MATERIAL	REMARKS	QTY
F	SHELL	SUS 304	Ni 50u"MIN.	1
E	ANODE	C7025	Ni 40u"	1
D	NEGATIVE	C7025	Ni 40u"	1
C	CENTER PIN	C5210	Au1u"(CONTACT AREA)/Sn80u"/Ni 40u"	1
B	COVER	PA10T	BLACK	1
A	HOUSING	PA10T	BLACK	1

A

B

C

D

E