







适用线路板(PCB LAYOUT)



适用扁平线(Applicable Flat Cable)

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC/DC。
4. 接触电阻: $\leq 0.03\Omega$ 。
5. 绝缘电阻: $\geq 500\text{M}\Omega$ 。

Part No	Pin	A	B	C
XY-FPC-1.0-CTD-4PH25	4	3.00	5.03	11.10
XY-FPC-1.0-CTD-5PH25	5	4.00	6.03	12.10
XY-FPC-1.0-CTD-6PH25	6	5.00	7.03	13.10
XY-FPC-1.0-CTD-7PH25	7	6.00	8.03	14.10
XY-FPC-1.0-CTD-8PH25	8	7.00	9.03	15.10
XY-FPC-1.0-CTD-9PH25	9	8.00	10.03	16.10
XY-FPC-1.0-CTD-10PH25	10	9.00	11.03	17.10
XY-FPC-1.0-CTD-11PH25	11	10.00	12.03	18.10
XY-FPC-1.0-CTD-12PH25	12	11.00	13.03	19.10
*****	****	***	*****	*****
XY-FPC-1.0-CTD-40PH25	40	(40-1)*1.0	(40+1)*1.0+0.03	(40+5)*1.0+0.10

序号	品名	材质
1	1.0线芯(H2.5)	LCP UL94V-0 本色
2	1.0下端子(H2.5)	铜合金/表面镀锡
3	1.0卧式后盖(H2.5)	LCP UL94V-0 黑色
4	1.0卧式弹片(H2.5)	铜合金/表面镀锡

DIMENSION IN mm	
TOLERANCE UNLESS OTHERWISE SPECIFIED	
.X±0.30	X.*±5°
.XX±0.20	.X.*±2°
.XXX±0.05	.XX.*±1°

厦门市辛译精密电子有限公司
Xiamen XinYi Xyconn Electronics Co.,Ltd

APR. Alex	TITLE: 1.0 Pitch H2.5 ZIF R/A Type Under CONN		
CHK. Jack	DWG NO. XY-FPC-1.0-CTD-NPH25		
DRA. Can	PROJ. 	CUSTOMER DRAWING	
	SIZE A4	SCALE 1:1	SHEET 1/1 REV. A