







REV.	DESCRIPTION	CHANGED	ECN/NO.	DATE
A0	NEW ISSUE			2012/8/17

NOTE:
1.MATERIAL:
1.1 HOUSING: LCP, UL 94V-0
COLOR: BLACK.
1.2 CONTACT: COPPER ALLOY, T=0.20mm.
1.3 SHIELD: COPPER ALLOY, T=0.40mm.
2.FINISH:
2.1 CONTACT: GOLD (1U") PLATING IN CONTACT AREA,
80u"MIN MATTE TIN PLATED IN SOLDER AREA,
30u" MIN. NICKEL UNDERPLATED OVERALL.
2.2 SHIELD: 50u" MIN. NICKEL UNDERPLATED OVERALL.
3.MECHANICAL CHARACTERISTICS
3.1 RATING CURRENT: 0.5A
3.2 RATING VOLTAGE: 40V
3.3 CONTACT RESISTANCE: 40 mΩ MAX
3.4 INSULATION RESISTANCE:
a, UNMATED: 100MΩ MIN AT 500 VDC
b, MATED: 10M OHMS MIN AT 150 VDC
3.5 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC/1MINUTE
3.6 DURABILITY: 10000 CYCLES.
3.7 OPERATING TEMPERATURE: -40°C--+85°C
3.8 STORAGE TEMPERATURE: -40°C--+65°C
4. NOTES:
4.1 ALL COMPONENTS ARE RoHS COMPLIANT.
4.2 RESISTANCE TO SOLDERING HEAT: 265°C FOR 10 SECONDS.





深圳市连欣科技有限公司



公差参考表				产品名称	DISPLAY PORT 20P FEMALE SMT外壳插板带螺丝孔2.65				
X	±0.35	ANGLE		产品编号	XDPF-0205-20S08				
X.X	±0.25	X°	±2°	模具图号		版本	A0	单位	MM
X.XX	±0.15	X.X°	±1.0°	审核		单重		比例	
X.XXX	±0.050	X.XX°	±0.50°	制图	胡志凤	类型		页数	1/2

REV.	DESCRIPTION	CHANGED	ECN/NO.	DATE
A0	NEW ISSUE			2012/8/17

客户出料方向



NOTES:

1.Material:



- 1.1 Carrier:Black Anti-Static Polystyrene.
- 1.2 Shipping carton:corrugated fiberboard

2.Dimension:


- 2.1 Carrier: Thickness:0.5±0.05mm.
- 2.2 Disk: Diameter Ø330mm.

3.Quantity:



- 3.1 Primary packing:190 PCS/Disk
- 3.2 Secondary packing:7Disk(1330PCS).




13" reel load per carton: 7 disk(1330PCS).



USER DIRECTION FOR FEED



深圳市连欣科技有限公司



公差参考表				产品名称	DISPLAY PORT 20P FEMALE SMT外壳插板带螺丝孔2.65 REEL				
X	±0.35	ANGLE		产品编号	XDPF-0205-20S08				
X.X	±0.25	X°	±2°	模具图号		版本	A0	单位	MM
X.XX	±0.15	X.X°	±1.0°	审核		单重		比例	
X.XXX	±0.050	X.XX°	±0.50°	制图	胡志凤	类型		页数	2/2