

表面压纹

M3 M4

技术要求:

1.额定电流:40A

2.材质:黄铜 T1.0mm

3.表面处理:镀锡

4.牙孔规格:M3/M4

螺丝尺寸




型号

M3

PCB-05-M3

M4

PCB-05-M4



PCB.WELDING DRAWING (TOLERANCE:±0.05)

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: PCB SOLDERING TERMINAL
			PAR PCB-05-MN
			DWN
			CHKD
DECIMALS:	ANGLES:		APVD
X.X±0.30	X.*±5°		SCALE N:A
X.XX±0.25	X.X°±1°		UNIT:MM
X.XXX±0.15			SIZE:A4
CUSTOMER COPY		SIZE:A4	SHEET:1F1
			REV:A