




技术要求:

- 1.打铜底 $0.5-1\mu\text{m}$,镍 $2-2.5\mu\text{m}$,镀雾锡 $3-5\mu\text{m}$ 2.
- 铆好后不得有松动现象.
- 2.插脚尖部符合可焊性要求.
- 3.螺纹需符合通止规/止针要求.
- 4.螺纹扭矩: 0.6Nm .
- 5.额定电流: 30A .



PCB.WELDING DRAWING (TOLERANCE: ± 0.05)

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: PCB SOLDERING TERMINAL
			PAR PCB-02-M3
DECIMALS:	ANGLES:		DWN
X.X ± 0.30	X.* $\pm 5^\circ$		CHKD
X.XX ± 0.25	X.X* $\pm 1^\circ$	CUSTOMER COPY	APVD
X.XXX ± 0.15			SCALE N:A
		SIZE:A4	UNIT:MM
		SHEET:1F1	REV:A