

表面压纹

M3 M4

技术要求:

- 1.打铜底0.5—1um,镍1.5—2.5um,镀锡2—5um.
- 2.铆好后不得有松动现象.
- 3.插脚尖部符合可焊性要求.
- 4.螺纹需符合通止规/止针要求.
- 5.M3螺纹扭矩:0.5Nm.
M4螺纹扭矩:1.0Nm.
- 6.额定电流:35A.
- 7.工作温度:—40℃—125℃

螺丝尺寸




型号

M3

PCB-01-M3

M4

PCB-01-M4



PCB.WELDING DRAWING (TOLERANCE:±0.05)

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: PCB SOLDERING TERMINAL	
		PAR	PCB-01-MN
		DWN	
		CHKD	
DECIMALS:	ANGLES:	APVD	
X.X±0.30	X.*±5°	SCALE N:A	UNIT:MM
X.XX±0.25	X.X*±1°	SIZE:A4	UNIT:MM
X.XXX±0.15		CUSTOMER COPY	UNIT:MM
		SIZE:A4	UNIT:MM
		SHEET:1F1	REV:A