










技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 105^{\circ}\text{C}$ 。
3. 额定电流: 0.5A
4. 额定电压: 50V, AC.
5. 接触电阻: 50mΩ MAX.
6. 绝缘电阻: 500MΩ Min.
7. 耐压: 150V AC/1Minute



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

P/N	PIN	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F
JXT-FC05-EC4PH20	4	6.30	2.57	1.50	0.70	4.10	4.10
JXT-FC05-EC5PH20	5	6.80	3.07	2.00	5.20	4.60	4.60
JXT-FC05-EC6PH20	6	7.30	3.57	2.50	5.70	5.10	5.10
JXT-FC05-EC7PH20	7	7.80	4.07	3.00	6.20	5.60	5.60
JXT-FC05-EC8PH20	8	8.30	4.57	3.50	6.70	6.10	6.10
JXT-FC05-EC9PH20	9	8.80	5.07	4.00	7.20	6.60	6.60
JXT-FC05-EC10PH20	10	9.30	5.57	4.50	7.70	7.10	7.10
JXT-FC05-EC11PH20	11	9.80	6.07	5.00	8.20	7.60	7.60
JXT-FC05-EC12PH20	12	10.30	6.57	5.50	8.70	8.10	8.10
JXT-FC05-EC13PH20	13	10.80	7.07	6.00	9.20	8.60	8.60
JXT-FC05-EC14PH20	14	11.30	7.57	6.50	9.70	9.10	9.10
JXT-FC05-EC15PH20	15	11.80	8.07	7.00	10.20	9.60	9.60
.....							
JXT-FC05-EC76PH20	76	42.30	51.00	37.50	40.70	40.10	40.10
JXT-FC05-EC77PH20	77	42.80	51.50	38.00	41.20	40.60	40.60
JXT-FC05-EC78PH20	78	43.30	52.00	38.50	41.70	41.10	41.10
JXT-FC05-EC79PH20	79	43.80	52.50	39.00	42.20	41.60	41.60
JXT-FC05-EC80PH20	80	44.30	53.00	39.50	42.70	42.10	42.10

序号	品名	材质
1	0.5掀盖卧式带扣胶芯(H=2.0)	LCP UL94V-0 本色
2	0.5掀盖卧式带扣后盖(H=2.0)	LCP UL94V-0 黑色
3	0.5掀盖卧式带扣端子(H=2.0)	铜合金/表面镀金
4	0.5掀盖卧式带扣焊片(H=2.0)	铜合金/表面镀锡
TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd
X.±0.50	±1°	
X.X±0.20		PART NO. JXT-FC05-ECNPH20
X.XX±0.10		TITLE: 0.5 Pitch掀盖卧式下接带扣(H=2.0)
UNITS	mm	DESIGN: Ethan
MATERILA	---	CHED: Olvia
FINISH	---	APPD: Ava
		MANUFACTURE DWG
		 SCALE N:A
		SHEET 1/1