




技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围:  $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$ .
3. 额定电流: 0.5A
4. 额定电压: 50V, AC.
5. 接触电阻:  $50\text{m}\Omega$  MAX.
6. 绝缘电阻:  $500\text{M}\Omega$  Min.
7. 耐电压: 150V AC/1Minute



| REV. | ECN NO. | DESCRIPTION | DATE | DESIGN |
|------|---------|-------------|------|--------|
|      |         |             |      |        |

| P/N                | PIN   | DIM A | DIM B | DIM C | DIM D | DIM E | DIM F |
|--------------------|-------|-------|-------|-------|-------|-------|-------|
| JXT-FC05-EC5PH255  | 5     | 7.45  | 3.07  | 2.00  | 7.10  | 4.60  | 4.50  |
| JXT-FC05-EC6PH255  | 6     | 7.95  | 3.57  | 2.50  | 7.60  | 5.10  | 5.00  |
| JXT-FC05-EC7PH255  | 7     | 8.45  | 4.07  | 3.00  | 8.10  | 5.60  | 5.50  |
| JXT-FC05-EC8PH255  | 8     | 8.95  | 4.57  | 3.50  | 8.60  | 6.10  | 6.00  |
| JXT-FC05-EC9PH255  | 9     | 9.45  | 5.07  | 4.00  | 9.10  | 6.60  | 6.50  |
| JXT-FC05-EC10PH255 | 10    | 9.95  | 5.57  | 4.50  | 9.60  | 7.10  | 7.00  |
| JXT-FC05-EC11PH255 | 11    | 10.45 | 6.07  | 5.00  | 10.10 | 7.60  | 7.50  |
| JXT-FC05-EC12PH255 | 12    | 10.95 | 6.57  | 5.50  | 10.60 | 8.10  | 8.00  |
| JXT-FC05-EC13PH255 | 13    | 11.45 | 7.07  | 6.00  | 11.10 | 8.60  | 8.50  |
| JXT-FC05-EC14PH255 | 14    | 11.95 | 7.57  | 6.50  | 11.60 | 9.10  | 9.00  |
| JXT-FC05-EC15PH255 | 15    | 12.45 | 8.07  | 7.00  | 12.10 | 9.60  | 9.50  |
| JXT-FC05-EC16PH255 | 16    | 12.95 | 8.57  | 7.50  | 12.60 | 10.10 | 10.00 |
| .....              | ..... | ..... | ..... | ..... | ..... | ..... | ..... |
| JXT-FC05-EC76PH255 | 76    | 42.95 | 38.57 | 37.50 | 42.60 | 40.10 | 40.00 |
| JXT-FC05-EC77PH255 | 77    | 43.45 | 39.07 | 38.00 | 43.10 | 40.60 | 40.50 |
| JXT-FC05-EC78PH255 | 78    | 43.95 | 39.57 | 38.50 | 43.60 | 41.10 | 41.00 |
| JXT-FC05-EC79PH255 | 79    | 44.45 | 40.07 | 39.00 | 44.10 | 41.60 | 41.50 |
| JXT-FC05-EC80PH255 | 80    | 44.95 | 40.57 | 39.50 | 44.60 | 42.10 | 42.00 |

| 序号 | 品名                  | 材质             | TOLERANCE      |     | 深圳聚兴泰电子科技有限公司<br>Shenzhen Juxingtai Electronic Technology Co., Ltd |                           |
|----|---------------------|----------------|----------------|-----|--------------------------------------------------------------------|---------------------------|
| 1  | 0.5掀盖卧式带扣胶芯(H=2.55) | LCP UL94V-0 本色 | X.±0.50        | ±1° | PART NO.                                                           | TITLE:                    |
| 2  | 0.5掀盖卧式后盖带扣(H=2.55) | LCP UL94V-0 黑色 | X.X±0.20       |     | JXT-FC05-ECNPH255                                                  | 0.5 Pitch掀盖卧式下接带扣(H=2.55) |
| 3  | 0.5掀盖卧式端子带扣(H=2.55) | 铜合金/表面镀金       | X.XX±0.10      |     | DESIGN: Ethan                                                      | MANUFACTURE DWG           |
| 4  | 0.5掀盖卧式焊片带扣(H=2.55) | 铜合金/表面镀锡       | UNITS mm       |     | CHED: Olivia                                                       |                           |
|    |                     |                | MATERILA — — — |     | APPD: Ava                                                          |                           |
|    |                     |                | FINISH — — —   |     |                                                                    |                           |
|    |                     |                |                |     |                                                                    | SCALE N:A                 |
|    |                     |                |                |     |                                                                    | SHEET 1/1                 |